



Datasheet

RS PRO 12 Pc 1000V VDE Insulated Pliers and Screwdriver Set

EN



⊕ x2
⊖ x3

This set of insulated RS PRO precision tools is supplied in a VDE approved vinyl wallet for secure transport and storage and features a wide variety of tools to be able to complete most applications, especially when working with live electrics or energised circuits. The cutters, pliers and screwdrivers are ideal for working up to 1000 V AC or 1500 V DC, making them essential tools for safe working in a professional or home DIY capacity.

Features

Cutters and Pliers

- Chrome finish
- Special tool steel
- DuoTech soft grip handles
- VDE Approved

Features

Screwdrivers

- Chrome Vanadium

Molybdenum steel blade
(phosphate finish)

- Soft grip handle
- VDE Approved

Automatic Wire Stripper - Features and Benefits:

- RS PRO Automatic wire stripper for all common stranded and solid conductors of 0.2 mm to 6.0 mm² (24 AWG - 10 AWG)
- Adjustable length stop of 5 mm to 12 mm (removable if necessary) for added versatility dependant on application
- Easily accessible built-in side cutter for max. 2 mm Ø

Compact Utility Knife - Features and Benefits:

- A sharp blade that can cut through materials clean and quick
- Stainless steel blade housing
- Auto-lock mechanism to ensure optimum safety whilst in use
- Ergonomic handle for enhanced comfort and control
- A safe and secure mechanism for changing blades
- Comes with 2× 18mm replacement blades

Compact Tape Measure - Features and Benefits:

- EEC II accuracy class
- Measurement in Metric units
- Double-stop
- Ergonomic and durable ABS case with no-slip ridges to allow for accurate measurement when handling the tape case



RS CODE NO	CONTENT	Description	Size
1253100	1253066	VDE Insulated Combination Pliers	180mm
	1253069	VDE Insulated Diagonal Cutter	160mm
	1253072	VDE Insulated Long Nose Pliers	160mm
	1253078	VDE Insulated Slotted Screwdriver	2.5×75mm
	1253081	VDE Insulated Slotted Screwdriver	4.0×100mm
	1253082	VDE Insulated Slotted Screwdriver	5.5×125mm
	1253086	VDE Insulated Pozidriv Screwdriver	PZ1×80mm
	1253087	VDE Insulated Pozidriv Screwdriver	PZ2×100mm
	1829774	VDE Voltage Tester (Short)-3X140m	3×140mm
	1763400	Automatic Wire Stripper	170mm
	1923667	Compact Snap-Off Knife 18Mm	18mm
	1923657	Tape Measure (Inch/Metric)3M-10Ft	3mx16mm

Attributes

Plier Type	Plier Set
Number of Pieces	12
ESD Safe	No
VDE/1000V Approved	Yes
Height Safe	No
Non Sparking:	No