

64210ULT

ULTRA LIFE | Halogen headlight lamps for cars



Areas of application

- Headlight
- Ideal for use in clear-glass headlights

Product benefits

- An ideal daytime running lamp due to long life span
- Up to triple the lifetime (compared to standard halogen lamps)
- 3 year guarantee (on halogen headlight lamps)

Product features

- Modern design with a silver cap (H4/H7)

Technical data

Electrical data


Power input	58 W ¹⁾
Nominal wattage	55 W
Nominal voltage	12 V
Test voltage	13.2 V

¹⁾ Maximum

Light technical data

Color temperature	3200 K
Luminous flux	1500 lm
Luminous flux tolerance	±10 %

Dimensions & weight



Product line drawing

Length	59.0 mm
Diameter	12.0 mm
Product weight	12.50 g

Lifespan

Lifespan B3	700 h
Lifespan Tc	1100 h

Additional product data

Base (standard designation)	PX26d
-----------------------------	-------

Product datasheet

Certificates & standards

ECE category	H7
--------------	----

Country specific categorizations

Order reference	64210ULT
-----------------	----------

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321416148	OSRA64210ULTDUO	-	-	-
4008321416261	OSRA64210ULT	-	-	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321416087	64210ULT	Blister 1	95 mm x 55 mm x 135 mm	0.71 dm ³	18.00 g
4008321416094	64210ULT	Shipping carton box 10	113 mm x 148 mm x 279 mm	4.67 dm ³	315.00 g
4008321416148	64210ULT	Unpacked 2	95 mm x 39 mm x 115 mm	0.43 dm ³	109.00 g
4008321416155	64210ULT	Shipping carton box 20	240 mm x 106 mm x 250 mm	6.36 dm ³	1246.00 g
4008321416261	64210ULT	Folding carton box 1	34 mm x 9 mm x 58 mm	0.02 dm ³	15.50 g
4008321416278	64210ULT	Bundle 10	174 mm x 64 mm x 170 mm	1.89 dm ³	155.00 g
4008321416285	64210ULT	Shipping carton box 100	129 mm x 186 mm x 356 mm	8.54 dm ³	1727.00 g
4008321416292	64210ULT	Blister 2	59 mm x 45 mm x 140 mm	0.37 dm ³	42.00 g
4008321416308	64210ULT	Shipping carton box 20	145 mm x 145 mm x 363 mm	7.63 dm ³	568.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

Guarantee terms are available at

▶ www.osram.com/am-guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.