


Atlantic, Atlantic stainless steel, Marina

common equipment for cabinets (continued)


Assembled chassis with rails and Lina 25 uprights




Dimensions of cabinets Height x Width (mm)	Uprights height		Rail length		Chassis fixing	
	A (mm)	D (mm)	B (mm)	C (mm)		
300 x 300	237	243	225	225		
300 x 400	237	343	225	325		
400 x 300	337	243	325	225		
400 x 400	337	343	325	325		
400 x 600	337	543	325	525		
500 x 400	437	343	425	325		
500 x 500	437	443	425	425		
600 x 400	537	343	525	325		
600 x 600	537	543	525	525		
600 x 800	537	743	525	725		
600 x 1000	537	943	525	925		
700 x 500	637	443	625	425		
800 x 600	737	543	725	525		
800 x 800	737	743	725	725		
800 x 1000	737	943	725	925		
1000 x 600	937	543	925	525		
1000 x 800	937	743	925	725		
1000 x 1000	937	943	925	925		
1000 x 1200	937	1143	925	1125		
1200 x 800	1137	743	1125	725		
1200 x 1000	1137	943	1125	925		
1200 x 1200	1137	1143	1125	1125		
1400 x 800	1337	743	1325	725		
1400 x 1000	1337	943	1325	925		

Lina 25 sectioned uprights and uprights to be cut


Cat.No 361 92



Cat.Nos 361 50/51/52/
53/54/55/56




Cat.No 361 58/59




(1) Saw notch for upright length x pitch 25,
the 2 others for uprights Cat.Nos 361 50/51/52/53/54/55/56

Rails


Cat.No 374 02




Cat.Nos 367 80/81/82/83/84/85/86
and 374 07



Cat.No 477 22



Cat.No 477 23



locking accessories

Pack Cat.Nos Lock housings for rebate locks or key barrels

10	368 04	For Atlantic, Atlantic stainless steel and Marina cabinets Lock	
10	368 05	Knob (with blanking plate)	
10	368 06	Knob fitted with key barrel 2433 A	
1	365 11	Padlocking Takes 3 safety padlocks Cat.No 227 97 (p. 154) Shackle Ø6 mm max. For fitting on Atlantic, Atlantic stainless steel and Marina knob or lock RAL 7021 painted steel	
1	365 13	Padlock adaptor stainless steel for Marina cabinets height ≥ 400 mm additional to latches Takes 3 padlocks Ø6 max.	

Locking latches

10	365 30	For Marina cabinets	
10	368 43	For Atlantic 1-door cabinet	

Metal rebate locks

10	368 17 ⁽¹⁾	Triangle male 6.5 mm	
10	368 18 ⁽¹⁾	Triangle male 8 mm	
10	368 19 ⁽¹⁾	Triangle male 11 mm (EDF)	
10	368 20 ⁽¹⁾	Double bar	

Key barrels

		Supplied with set of 2 keys For key No	
10	368 22 ⁽¹⁾	405	
10	368 23 ⁽¹⁾	421	
10	368 24 ⁽¹⁾	455	
10	368 25 ⁽¹⁾	1242 E	
10	368 26 ⁽¹⁾	2433 A	
10	368 27 ⁽¹⁾	3113 A	
10	365 45 ⁽¹⁾	Set of two 2433 A keys Other key code: please consult us	

Metal keys for rebate locks

10	365 39	Triangle male 6.5 mm	
10	365 40	Triangle male 8 mm	
10	365 41	Triangle male 11 mm (EDF)	
10	365 42	Double bar	
1	368 42	Multi-size key for rebate locks: square male 8 mm, square male 6 mm, Triangle male 8 mm and double bar	

(1) Except Marina enclosures: please consult us