

MTS SPORTY RANGE

MTS Trail - regular width

MTS Trail - XXL width

S3S SR FO HI CI ESD



DESCRIPTION

Based in southwest France since the company was founded in 1955, ANNIC SAS, better known as MTS More Than Safety is today one of Europe's foremost safety Footwear brands under the Honeywell portfolio. A sports line designed exclusively by MTS: the unique design and colours of MTS sporty range models combine aesthetics research, ergonomics and technological efficiency. As a result: a high-performance look and hightech materials, inspired by high-level sports. MTS Trail S3S is a non-metallic safety shoe with a composite toe and an SR rated slip resistant outsole. Made in France and manufactured according to ISO 9001.



MTS Trail

FEATURES

- Suitable for Indoor/Outdoor use
- Ideal for: Logistics, Services, Warehouses and Transportation industries
- Composite toe cap protects against impact and compression
- Flexible and lightweight non metallic safety shoe, casual sporty design
- TPU heel counter for increased support, flexibility and comfort
- ESD marking
- Accessory: Two types of insoles certified according to DGUV 112-191: covers the user of orthopedic insoles in the workplace. When fitted with VAUPEL orthopedic insoles, has been tested and certified to continue to meet the requirements of the standard
- Accessory: Modular three width Insock Fitting System: standard, wide or narrow – increases the comfort from wearing the shoe
- Available in regular width and in XXL width

 Antistatic properties

 Anti-puncture resistance with PS level

 Heel energy absorption

 Cleated outsole SR: Excellent Slip Resistance

 Resistance to fuel oil

 Heat Insulated Sole, Cold Insulated Sole.

 ESD: Certification of Electrical resistance

TECHNICAL SPECIFICATIONS

Upper	onDura Nilo Grey, onSuede 1.7 mm, water-resistant and breathable
Lining	Blue colour full Artico lining and Black color OnMICRO Suede black on Heel counter
Fastening	Plastic hooks and round tubular laces Black colour
Toe Cap	Toe cap resistant to an impact of 200 Joules, Composite Toe Cap
Midsole	Anti-perforation, non-metallic onPROTECTOR DIAMOND, type PS
Insock	Thermoformed PU foam, anatomic, antistatic, TITAN
Sole	Made from a combination of polyurethane (PU-PU), oil resistant FO, antistatic, ESD
Sole pattern	Multi-purpose, slip resistance conforms to SR standard
Weight (per one shoe)	Approximately 650 g
Colors	Black Blue
Sizes	35-50 (3-15UK)
Standard	EN ISO 20345:2022, S3S SR FO HI CI ESD
Style	Low-Cut

ORDERING INFORMATION

DESCRIPTION	REF. IN SAP	REF. IN ECHINOPS	SIZE
MTS Trail - regular width	6270619	4585303	35-50
MTS Trail - XXL width	6270622	4585603	35-50

MTS BY HONEYWELL SAFETY PRODUCTS UNITED KINGDOM

Honeywell House, Skimped Hill Lane,
Bracknell, Berkshire RG12 1EB
Phone: +44 (0) 1256 274938
Email: info-uk.hsp@honeywell.com

ANNIC S.A.S.

1 rue des Usines
82250 Laguepie – France
Tel.: +33 (0) 563 302 101
Fax.: +33 (0) 563 314 018
Email : contact@mts-morethansafety.com

MTS BY HONEYWELL SAFETY PRODUCTS NORDIC AB

Box 15 147
SE-167 15 Bromma – Sverige
Phone: +46 (0) 424480433
Email: info-nordic.hsp@honeywell.com

For More Information

sps.honeywell.com

For Information on Innovations and Patents

hsmpats.com

MTS BY HONEYWELL SAFETY PRODUCTS BENELUX BV

Lange Amerikaweg 55
7332 BP Apeldoorn, Nederland
Tel: +31 (0) 20 5656 988
Email: info-benelux.hsp@honeywell.com

