

SHOWA

386

CUT PROTECTION

Cut resistant glove with duracoil liner and embossed nitrile foam palm


Cut resistance level C thanks to the DURACoil liner with a microporous nitrile coating for great grip and aeration.

Features

- ▲ Multifilament polyester wrapping DURACoil liner reinforced with HPPE provides effective protection against cuts
- ▲ Microporous nitrile coated palm for good grip & aeration while protecting the hand from oils and abrasions
- ▲ Offers maximum comfort when performing delicate tasks
- ▲ Embossed nitrile palm finish disperses oil away to increase grip and longevity in light oily environments
- ▲ Unique SHOWA ergonomic shape that replicates the natural curve of the human hand for enhanced dexterity and longer use
- ▲ Seamless knit designed to prevent irritation



Certifications



Suitable industries & applications

Industries

- ▲ Aerospace
- ▲ Automotive
- ▲ Construction

- ▲ Manufacturing
- ▲ Maritime

Applications

- ▲ Component and Product Assembly
- ▲ Vehicle Assembly
- ▲ Infrastructure Engineering
- ▲ General Maintenance

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Cut resistant glove with duracoil liner and embossed nitrile foam palm

Product information

Materials	Liner:	13 Gauge Engineered HPPE, Polyester
	Coating:	Microporous Nitrile
Colour	Grey / Black	
Length	310mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

S	SHO3861	Items per Pack 10 x Pairs
M	SHO3862	
L	SHO3863	Items per Case 120 x Pairs
XL	SHO3864	
XXL	SHO3865	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.