

NEMA line Outlet 5-15R, Snap-in Mounting, Front Side, V-Slot Terminal



Description

- Panel Mount:
Snap-in, Front Side
- 1 Function:
Line Outlet, Protection class I
- V-Slot- Connector

Approvals

- UL File Number: E96454
- CSA File Number: 73690

Characteristics

- Designed for standard applications


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Detailed request for product](#)

Technical Data

Ratings IEC	15 A / 250 VAC; Hz
Ratings UL/CSA	15 A / 125 VAC; 60 Hz
Allowable Operation Temp.	-25 °C to +60 °C
Degree of Protection	from front side IP 20 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Terminal	V-Slot- Connector
Panel Thickness s	Snap-in 0.8 mm to 1.6 mm
Material: Housing	Thermoplastic, black

Dimensions



Panel thickness X
0.8 - 1.2 mm: 24.6 mm
1.3 - 1.6 mm: 24.8 mm

Assembly Instructions



Installation Diagram: V-slotted terminals for connecting multiple receptacles (only for solid bare wires from type 14 AWG)

All Variants

Type	Protection Class	Panel mounting	Panel Thickness s [mm]	Terminal	Order Number
0709-1	I	Snap-in	0.8 -1.6	V-Slot- Connector	4300.0702

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 120 Pcs

Mating Inlets/Plugs

Category / Description

[Power Supply Cord Overview complete](#)



EU Power Supply Cord with IEC Connector C19, straight/ angled	6004.0395
US Power Supply Cord with IEC Connector C19, straight	6009.5195
US Power Supply Cord with IEC Connector C13, straight	6009.1315
JP Power Supply Cord with IEC Connector C13, straight	6047.6414

[Power Supply Cord further types to 0709-1](#)

[Power Supply or Interconnection Cord Overview complete](#)



Diverse Power Supply and Interconnection Cords 2.5 A	CS01.0221.150
Diverse Power Supply and Interconnection Cords 2.5 A	CS02.0221.150

[Power Supply or Interconnection Cord further types to 0709-1](#)