

BMP51 LABEL PRINTER



Designed to get the job done

When you need clear, durable labels on the spot, you need the BMP™51 Label Maker from Brady. It offers crisp printing, easy formatting, convenient label sizes, and portability required for electrical and datacom installations, laboratory identification, facility and safety labelling.



Order Reference	Description	Manufacturer Reference	Width (mm)	Length (m)	Height (mm)	Printer Compatibility
B-595 Vinyl Tape, Control Panel & Electrical Panel Labels; Indoor & Outdoor Grade Facility & Safety Identification						
7753518	Black/Clear Permanent Vinyl Tape	MC-1500-595-CL-BK	38.1 mm	6.1 m		BMP51; BMP53
7753596	Black/Clear Permanent Vinyl Tape	MC-500-595-CL-BK	12.7 mm	6.1 m		BMP41; BMP51; BMP53
7753641	Black/Clear Permanent Vinyl Tape	MC-750-595-CL-BK	19.5 mm	6.1 m		BMP41; BMP51; BMP53
7934247	Black/Clear Permanent Vinyl Tape 6.09m	MC1-1000-595-CL-BK	25.4 mm	6.1 m		BMP41; BMP51; BMP53
7753524	Black/Orange Permanent Vinyl Tape	MC-1500-595-OR-BK	38.1 mm	7.62 m		BMP51; BMP53
7753603	Black/Orange Permanent Vinyl Tape	MC-500-595-OR-BK	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753657	Black/Orange Permanent Vinyl Tape	MC-750-595-OR-BK	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934253	Black/Orange Permanent Vinyl Tape 7.62m	MC1-1000-595-OR-BK	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753537	Black/White Permanent Vinyl Tape	MC-1500-595-WT-BK	38.1 mm	7.62 m		BMP51; BMP53
7753616	Black/White Permanent Vinyl Tape	MC-500-595-WT-BK	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753669	Black/White Permanent Vinyl Tape	MC-750-595-WT-BK	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934250	Black/White Permanent Vinyl Tape 7.62m	MC1-1000-595-WT-BK	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753534	Black/Yellow Permanent Vinyl Tape	MC-1500-595-YL-BK	38.1 mm	7.62 m		BMP51; BMP53
7753613	Black/Yellow Permanent Vinyl Tape	MC-500-595-YL-BK	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753672	Black/Yellow Permanent Vinyl Tape	MC-750-595-YL-BK	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934269	Black/Yellow Permanent Vinyl Tape 7.62m	MC1-1000-595-YL-BK	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753530	Red/White Permanent Vinyl Tape	MC-1500-595-WT-RD	38.1 mm	7.62 m		BMP51; BMP53
7753619	Red/White Permanent Vinyl Tape	MC-500-595-WT-RD	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753663	Red/White Permanent Vinyl Tape	MC-750-595-WT-RD	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934262	Red/White Permanent Vinyl Tape 7.62m	MC1-1000-595-WT-RD	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753506	White/Black Permanent Vinyl Tape	MC-1500-595-BK-WT	38.1 mm	7.62 m		BMP51; BMP53
7753584	White/Black Permanent Vinyl Tape	MC-500-595-BK-WT	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753644	White/Black Permanent Vinyl Tape	MC-750-595-BK-WT	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934234	White/Black Permanent Vinyl Tape 7.62m	MC1-1000-595-BK-WT	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753515	White/Blue Permanent Vinyl Tape	MC-1500-595-BL-WT	38.1 mm	7.62 m		BMP51; BMP53
7753593	White/Blue Permanent Vinyl Tape	MC-500-595-BL-WT	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753647	White/Blue Permanent Vinyl Tape	MC-750-595-BL-WT	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934238	White/Blue Permanent Vinyl Tape 7.62m	MC1-1000-595-BL-WT	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753512	White/Clear Permanent Vinyl Tape	MC-1500-595-CL-WT	38.1 mm	6.1 m		BMP51; BMP53
7753590	White/Clear Permanent Vinyl Tape	MC-500-595-CL-WT	12.7 mm	6.1 m		BMP41; BMP51; BMP53
7753650	White/Clear Permanent Vinyl Tape	MC-750-595-CL-WT	19.5 mm	6.1 m		BMP41; BMP51; BMP53
7934240	White/Clear Permanent Vinyl Tape 6.09m	MC1-1000-595-CL-WT	25.4 mm	6.1 m		BMP41; BMP51; BMP53
7753521	White/Green Permanent Vinyl Tape	MC-1500-595-GN-WT	38.1 mm	7.62 m		BMP51; BMP53
7753600	White/Green Permanent Vinyl Tape	MC-500-595-GN-WT	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753653	White/Green Permanent Vinyl Tape	MC-750-595-GN-WT	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934244	White/Green Permanent Vinyl Tape 7.62m	MC1-1000-595-GN-WT	25.4 mm	7.62 m		BMP41; BMP51; BMP53
7753528	White/Red Permanent Vinyl Tape	MC-1500-595-RD-WT	38.1 mm	7.62 m		BMP51; BMP53
7753607	White/Red Permanent Vinyl Tape	MC-500-595-RD-WT	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753666	White/Red Permanent Vinyl Tape	MC-750-595-RD-WT	19.5 mm	7.62 m		BMP41; BMP51; BMP53
7934256	White/Red Permanent Vinyl Tape 7.62m	MC1-1000-595-RD-WT	25.4 mm	7.62 m		BMP41; BMP51; BMP53
B-584 Reflective Vinyl Tape, Facility & Safety Identification; General Identification						
7753451	Black/Yellow Reflective Vinyl Tape	MC-1000-584-YL	25.4 mm	6.1 m		BMP51; BMP53
7753502	Black/Yellow Reflective Vinyl Tape	MC-1500-584-YL	38.1 mm	6.1 m		BMP51; BMP53
7753580	Black/Yellow Reflective Vinyl Tape	MC-500-584-YL	12.7 mm	6.1 m		BMP41; BMP51; BMP53
7753635	Black/Yellow Reflective Vinyl Tape	MC-750-584-YL	19.5 mm	6.1 m		BMP41; BMP51; BMP53
7753458	Black/White Reflective Vinyl Tape	MC-1000-584	25.4 mm	6.1 m		BMP51; BMP53
7753509	Black/White Reflective Vinyl Tape	MC-1500-584	38.1 mm	6.1 m		BMP51; BMP53
B-422 Gloss Polyester Tape, Product Identification; Voice & Data Communication						
7753565	Black/White Glossy Polyester Tape	MC-375-422	9.53 mm	7.62 m		BMP41; BMP51; BMP53
7753571	Black/White Glossy Polyester Tape	MC-475-422	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753574	Black/White Glossy Polyester Tape	MC-500-422	12.7 mm	7.62 m		BMP41; BMP51; BMP53
7753625	Black/White Glossy Polyester Tape	MC-625-422	15.88 mm	7.62 m		BMP41; BMP51; BMP53
7934231	Black/White Glossy Polyester Tape 7.62m	MC1-1000-422	25.4 mm	7.62 m		BMP41; BMP51; BMP53
B499 Matt Nylon Cloth Tape, Wire & Cable Marking; General Labelling; Laboratory Identification						
7753449	Black/White Nylon Cloth Printer Tape	MC-1000-499	25.4 mm	4.88 m		BMP51; BMP53
7753568	Black/White Nylon Cloth Printer Tape	MC-375-499	9.53 mm	4.88 m		BMP41; BMP51; BMP53
7753578	Black/White Nylon Cloth Printer Tape	MC-500-499	12.7 mm	4.88 m		BMP41; BMP51; BMP53
7753638	Black/White Nylon Cloth Tape	MC-750-499	19.5 mm	4.88 m		BMP41; BMP51; BMP53
B-498 Semi-Gloss Vinyl Cloth Tape, Repositionable, Terminal Block Markers						
8011654	MC-240-498 Terminal markers black /white	MC-240-498	6.1 mm	4.88 m		BMP41; BMP51; BMP53
8011657	MC-318-498 Terminal markers black /white	MC-318-498	8.8 mm	4.88 m		BMP41; BMP51; BMP53
8011660	MC-375-498 Terminal marker black/white	MC-375-498	9.53 mm	6.1 m		BMP41; BMP51; BMP53
B-422 Gloss Polyester Labels, Product Identification; Voice & Data Communication						
7934137	Black/White Polyester Printer Labels	M-47-422	25.4 mm		12.7 mm	BMP41; BMP51; BMP53
7934143	Black/White Polyester Printer Labels	M-49-422	25.4 mm		25.4 mm	BMP41; BMP51; BMP53

7934165	Black/White Polyester Printer Labels	M-89-422	12.7 mm	38.1 mm	BMP41; BMP51; BMP53	
7934177	Black/White Polyester Printer Labels	M-90-422	19.5 mm	38.1 mm	BMP41; BMP51; BMP53	
7753391	Black/White Polyester Printer Labels	M-7-422	12.7 mm	12.7 mm	BMP41; BMP51; BMP53	
B-499 Matt Nylon Cloth Labels, Wire & Cable Marking; General Labelling; Laboratory Identification						
7753265	Black/White Nylon Cloth Printer Labels	M-131-499	12.7 mm	25.4 mm	BMP41; BMP51; BMP53	
7753269	Black/White Nylon Cloth Printer Labels	M-132-499	38.1 mm	31.75 mm	BMP51; BMP53	
7934193	Black/White Nylon Cloth Printer Labels	M-141-499	25.4 mm	57.15 mm	BMP41; BMP51; BMP53	
7934228	Black/White Nylon Cloth Printer Labels	M-128-499	25.4 mm	48.26 mm	BMP41; BMP51; BMP53	
8011645	M-11-499 Nylon cloth black on white	M-11-499	19.5 mm	12.7 mm	BMP41; BMP51; BMP53	
7753405	Black/White Nylon Cloth Printer Labels 9.53 mm Dia	M-82-499			BMP41; BMP51; BMP53	
7753420	Black/White Nylon Cloth Printer Labels 12.70 mm Dia	M-83-499			BMP41; BMP51; BMP53	
7753414	Black/Orange Nylon Cloth Printer Labels 9.53 mm Dia	M-82-499-OR-BK			BMP41; BMP51; BMP53	
7753423	Black/Orange Nylon Cloth Printer Labels 12.70 mm Dia	M-83-499-OR-BK			BMP41; BMP51; BMP53	
7753417	Black/Red Nylon Cloth Printer Labels 9.53 mm Dia	M-82-499-RD-BK			BMP41; BMP51; BMP53	
7753427	Black/Red Nylon Cloth Printer Labels 12.70 mm Dia	M-83-499-RD-BK			BMP41; BMP51; BMP53	
7753411	Black/Yellow Nylon Cloth Printer Labels 9.53 mm Dia	M-82-499-YL-BK			BMP41; BMP51; BMP53	
7753436	Black/Yellow Nylon Cloth Printer Labels 12.70 mm Dia	M-83-499-YL-BK			BMP41; BMP51; BMP53	
B-498 Semi-Gloss Vinyl Cloth Labels, Repositionable, Terminal Block Markers						
7753262	Black/White Vinyl Cloth Printer Labels	M-131-498	12.7 mm	25.4 mm	BMP41; BMP51; BMP53	
7753394	Black/White Vinyl Cloth Printer Labels	M-7-498	12.7 mm	12.7 mm	BMP41; BMP51; BMP53	
7934187	Black/White Vinyl Cloth Printer Labels	M-91-498	25.4 mm	38.1 mm	BMP41; BMP51; BMP53	
7934200	Black/White Vinyl Cloth Printer Labels	M-48-498	25.4 mm	19.5 mm	BMP41; BMP51; BMP53	
7934219	Black/White Vinyl Cloth Printer Labels	M-49-498	25.4 mm	25.4 mm	BMP41; BMP51; BMP53	
7934225	Black/White Vinyl Cloth Printer Labels	M-128-498	25.4 mm	48.26 mm	BMP41; BMP51; BMP53	
8011641	M-11-498 Vinyl cloth labels black/white	M-11-498	19.5 mm	12.7 mm	BMP41; BMP51; BMP53	
B-432 Gloss Polyester, General & Industrial Identification; Laboratory Identification; Product Identification; Rating & Nameplate Labels; Voice & Data Communication						
7753293	Black/Clear Polyester Printer Labels	M-17-432-CL-BK	25.4 mm	12.7 mm	BMP51; BMP53	
7753398	Black/Clear Polyester Printer Labels	M-78-432-CL-BK	25.4 mm	48.26 mm	BMP51; BMP53	
B-428 Matt Metallised Polyester, Automation & Electrical Component Markers; Control Panel & Electrical Panel Labels; Rating & Nameplate Labels						
7753350	Black/Silver Metallised Polyester Labels	M-29-428	38.1 mm	12.7 mm	BMP51; BMP53	
7934146	Black/Silver Metallised Polyester Labels	M-47-428	25.4 mm	12.7 mm	BMP41; BMP51; BMP53	
7934155	Black/Silver Metallised Polyester Labels	M-60-428	25.4 mm	5.8 mm	BMP41; BMP51; BMP53	
8011676	M-92-428-BB Metallised poly black/silver	M-92-428-BB	12.7 mm	33.2 mm	BMP41; BMP51; BMP53	
B-483 Gloss Polyester, Ultra Aggressive Adhesive, Automation & Electrical Component Markers; Bin & Storage Identification; General & Industrial Identification						
7753382	Black/White Polyester Printer Labels	M-61-483	12.7 mm	5.8 mm	BMP41; BMP51; BMP53	
7934149	Black/White Polyester Printer Labels	M-47-483	25.4 mm	12.7 mm	BMP41; BMP51; BMP53	
7934159	Black/White Polyester Printer Labels	M-60-483	25.4 mm	5.8 mm	BMP41; BMP51; BMP53	
B-427 Matt Self-Laminating Vinyl, Wire & Cable Marking, Self-extinguishing, Voice & Data Communication						
7753231	Black/White Self-Laminating Vinyl Labels	M-102-427	12.7 mm	31.75 mm	BMP41; BMP51; BMP53	
7753247	Black/White Self-Laminating Vinyl Labels	M-115-427	38.1 mm	31.75 mm	BMP51; BMP53	
7753256	Black/White Self-Laminating Vinyl Labels	M-116-427	38.1 mm	63.5 mm	BMP51; BMP53	
7753271	Black/White Self-Laminating Vinyl Labels	M-134-427	44.45 mm	38.1 mm	BMP51; BMP53	
7753278	Black/White Self-Laminating Vinyl Labels	M-133-427	44.45 mm	25.4 mm	BMP51; BMP53	
7753372	Black/White Self-Laminating Vinyl Labels	M-32-427	38.1 mm	38.1 mm	BMP51; BMP53	
7753376	Black/White Self-Laminating Vinyl Labels	M-33-427	38.1 mm	11.6 mm	BMP51; BMP53	
7753385	Black/White Self-Laminating Vinyl Labels	M-34-427	38.1 mm	152.4 mm	BMP51; BMP53	
7934152	Black/White Self-Laminating Vinyl Labels	M-49-427	25.4 mm	25.4 mm	BMP41; BMP51; BMP53	
7934168	Black/White Self-Laminating Vinyl Labels	M-51-427	25.4 mm	63.5 mm	BMP41; BMP51; BMP53	
7934171	Black/White Self-Laminating Vinyl Labels	M-90-427	19.5 mm	38.1 mm	BMP41; BMP51; BMP53	
7934174	Black/White Self-Laminating Vinyl Labels	M-89-427	12.7 mm	38.1 mm	BMP41; BMP51; BMP53	
7934180	Black/White Self-Laminating Vinyl Labels	M-91-427	25.4 mm	38.1 mm	BMP41; BMP51; BMP53	
7934196	Black/White Self-Laminating Vinyl Labels	M-136-427	25.4 mm	19.5 mm	BMP41; BMP51; BMP53	
7934199	Black/White Self-Laminating Vinyl Labels	M-143-427	25.4 mm	31.75 mm	BMP41; BMP51; BMP53	
7934203	Black/White Self-Laminating Vinyl Labels	M-47-427	12.7 mm	25.4 mm	BMP41; BMP51; BMP53	
7934206	Black/White Self-Laminating Vinyl Labels	M-48-427	19.5 mm	25.4 mm	BMP41; BMP51; BMP53	
7934212	Black/White Self-Laminating Vinyl Labels	M-53-427	25.4 mm	11.6 mm	BMP41; BMP51; BMP53	
7934216	Black/White Self-Laminating Vinyl Labels	M-53-427-YL	25.4 mm	11.6 mm	BMP41; BMP51; BMP53	
7753243	Black White Self-Laminating Vinyl Labels	M-11-427	12.7 mm	19.5 mm	BMP41; BMP51; BMP53	
7934161	Black/Yellow Self-Laminating Vinyl Label	M-51-427-YL	25.4 mm	63.5 mm	BMP41; BMP51; BMP53	
7934183	Black/Yellow Self-Laminating Vinyl Label	M-91-427-YL	25.4 mm	38.1 mm	BMP41; BMP51; BMP53	
7753445	Black/White Self-Laminating Vinyl Tape	MC-1000-427	25.4 mm	7.62 m	BMP51; BMP53	
7753499	Black/White Self-Laminating Vinyl Tape	MC-1250-427	31.75 mm	7.62 m	BMP51; BMP53	
7753629	Black/White Self-Laminating Vinyl Tape	MC-750-427	19.5 mm	7.62 m	BMP41; BMP51; BMP53	
B-342 Matt Heat-Shrink Polyolefin Sleeve, Wire & Cable Marking						
7753253	Blk/White Heatshrink Wire Marker Sleeve	M-125-1-342	25.78 mm	6 mm	BMP51; BMP53	
7753304	Blk/White Heatshrink Wire Marker Sleeve	M-187-1-342	25.78 mm	8.5 mm	BMP51; BMP53	
7753344	Blk/White Heatshrink Wire Marker Sleeve	M-250-1-342	25.78 mm	11.15 mm	BMP51; BMP53	
7753388	Blk/White Heatshrink Wire Marker Sleeve	M-375-1-342	25.78 mm	16.4 mm	BMP51; BMP53	
8011682	M-125-075-342 heatshrink black/white	M-125-075-342	19.5 mm	6 mm	BMP41; BMP51; BMP53	
8011679	M-187-075-342 heatshrink black/white	M-187-075-342	19.5 mm	8.5 mm	BMP41; BMP51; BMP53	
8011673	M-250-075-342 heatshrink black/white	M-250-075-342	19.5 mm	11.15 mm	BMP41; BMP51; BMP53	
8011685	M-375-075-342 heatshrink black/white	M-375-075-342	19.5 mm	16.4 mm	BMP41; BMP51; BMP53	
7753492	Blk/White Heatshrink Wire Marker Sleeve	MC-125-342		2.13 m	6 mm	BMP41; BMP51; BMP53
7753540	Blk/White Heatshrink Wire Marker Sleeve	MC-250-342		2.13 m	11.15 mm	BMP41; BMP51; BMP53
7753543	Blk/White Heatshrink Wire Marker Sleeve	MC-187-342		2.13 m	8.5 mm	BMP41; BMP51; BMP53
7753495	Blk/Yellow Heatshrink Wire Marker Sleeve	MC-125-342-YL		2.13 m	6 mm	BMP41; BMP51; BMP53
7753546	Blk/Yellow Heatshrink Wire Marker Sleeve	MC-187-342-YL		2.13 m	8.5 mm	BMP41; BMP51; BMP53
7753559	Blk/Yellow Heatshrink Wire Marker Sleeve	MC-250-342-YL		2.13 m	11.15 mm	BMP41; BMP51; BMP53
B-351 Matt Tamper-resistant Vinyl, Fractures easily, prevents one-piece removal, Product Identification; Laboratory Identification						
7753284	Blk/White Tamper-Resistant Vinyl Labels	M-17-351	25.4 mm	12.7 mm	BMP51; BMP53	
7753329	Black/White Tamper-Evident Vinyl Labels	M-20-351	25.4 mm	5.8 mm	BMP51; BMP53	
B-412 Polypropylene Tags, Non-Adhesive Slide-in Strips, Voice & Data Communication						
8011663	MC-475-412 Polyprop taglabel black/white	MC-475-412	12.7 mm	6.1 m	BMP41; BMP51; BMP53	
7753556	Black/White Polypropylene Tags	MC-375-412	9.53 mm	6.1 m	BMP41; BMP51; BMP53	
7753622	Black/White Polypropylene Tags	MC-625-412	15.88 mm	6.1 m	BMP41; BMP51; BMP53	
Accessories						
7753688	BMP51/53 Soft Carry Case	M50-SC			BMP51; BMP53	
7117590	BMP71 AC Adaptor UK	M41/50/61/71-AC-BC-UK			BMP41; BMP51; BMP53; BMP71	
7753675	Li-Ion Battery Pack/AC Adaptor - EU	UBP-LI-ION-AC-EUR			BMP51; BMP53	
7753679	Li-Ion Battery Pack/AC Adaptor - UK	UBP-LI-ION-AC-UK			BMP51; BMP53	

* BMP53 Now Discontinued 2017

** Additional BMP41 labels are available, see printer product page for full range