

Wiha fibre-glass-reinforced folding rulers.

2 m of perfection.



Often emulated but never surpassed – the Longlife Plus folding metre rule: has a long service life and is accurate and easy to use.



The world's first folding ruler made of high-quality fibre-glass material was developed and manufactured in 1968 and, since then, has been successfully marketed under the "Longlife" name.

Its characteristic joint with perfect long-life characteristics is still unique.

The Polyamide reinforced with 30% fibre-glass makes the Longlife ruler water resistant and scratch and score-proof.

Compared to wooden folding rulers a substantially higher service life is attained.


A deep embossed, precise scale on each segment contributes to the excellent performance characteristics.



Joints



Metal ends



Backwards running scale



Fixation

Angular display

Angle gauge

Wiha fibre-glass-reinforced folding rulers.

Permanent – Longlife

- no swelling from contact with water!
- distinctly longer service life compared to wooden folding ruler
- resistant to chemicals, washable

Longlife Plus

- red joint bodies for improved legibility
- wear-resistant metal ends
- backwards running scale

Longlife All in One

- angle measurement function
- depth measurement function

Exact

- CE conformity and Swiss precision for all rulers

Longlife All in One and Longlife Plus. Displays.



410 2007 Longlife All in One folding ruler, 2 m metric, 10 segments.

- Material: Glass fibre reinforced polyamide. Scratch, weather and chemical resistant.
- Joints: Play free, wear resistant and maintenance free joint with steel spring pin for constant tension. Usefull 90° snap-in position.
- Scale: Deep embossed black scale in 1 mm increments. Every 10 cm is marked in red.
- Accuracy: CE conformity, EU standard accuracy class III.
- Extra: Readable from both sides through a second, backwards running scale (Recto Verso).
Depth measurement with push-out depth gauge.
Angle measurement with anchoring of depth gauge in fixation hole.

Order-No.	1	2	3	4
33232 7	15	135	white	10



410 2001 Longlife Plus folding metre rule, 2 m, metric, 10 segments. With metal ends.

- Material: Glass fibre reinforced polyamide. Scratch, weather and chemical resistant.
- Joints: Play free, wear resistant and maintenance free joint with steel spring pin for constant tension. Usefull 90° snap-in position.
- Scale: Deep embossed black scale in 1 mm increments. Every 10 cm is marked in red.
- Accuracy: CE conformity, EU standard accuracy class III.
- Extra: Wear resistant metal ends on the first and last segments. Readable from both sides through a second, backwards running scale (Recto Verso).

Order-No.	1	2	3	4
27055 1	15	140	yellow	10
27059 9	15	140	white	10
27060 5	15	140	yellow/white	10



NEW
410 ... VH Sales counter display for Longlife folding rulers. Card display with 20 pcs. (2 m) or 54 pcs. (1 m).

Order-No.	Art.-No.	Content	4
33660 8	410 2007 2 VH	20 x 41020072 Longlife All in One, 2 m	1
33945 6	410 2001 1 VH	20 x 41020011 Longlife Plus, 2 m, yellow	1
34495 5	410 2000 2 VH	20 x 41020002 Longlife, 2 m, white	1
33946 3	410 1000 2 VH	54 x 41010002 Longlife, 1 m, white	1

Longlife.



410 2000 Longlife folding metre rule, 2 m, metric, 10 segments.

- Material: Glass fibre reinforced polyamide. Scratch, weather and chemical resistant.
- Joints: Play free, wear resistant and maintenance free joint with steel spring pin for constant tension. Usefull 90° snap-in position.
- Scale: Deep embossed black scale in 1 mm increments. Every 10 cm is marked in red.
- Accuracy: CE conformity, EU standard accuracy class III.

Order-No.	1	2	3	4
27058 2	15	140	yellow	10
27057 5	15	140	white	10



410 1000 Longlife folding metre rule, 1 m, metric, 10 segments.

- Material: Glass fibre reinforced polyamide. Scratch, weather and chemical resistant.
- Joints: Play free, wear resistant and maintenance free joint with steel spring pin for constant tension. Usefull 90° snap-in position.
- Scale: Deep embossed black scale in 1 mm increments. Every 10 cm is marked in red.
- Accuracy: CE conformity, EU standard accuracy class III.

Order-No.	1	2	3	4
27061 2	13	45	yellow	10
27062 9	13	45	white	10



410 1010 Longlife folding metre rule, 1 m, metric, 5 segments.

- Material: Glass fibre reinforced polyamide. Scratch, weather and chemical resistant.
- Joints: Play free, wear resistant and maintenance free joint with steel spring pin for constant tension. Usefull 90° snap-in position.
- Scale: Deep embossed black scale in 1 mm increments. Every 10 cm is marked in red.
- Accuracy: CE conformity, EU standard accuracy class III.

Order-No.	1	2	3	4
27063 6	15	65	yellow	20

Sale only in pack quantities!
Special scales available on request.