

PAT Tester

Printers and Barcode Scanners

Test n Tag Elite

An extremely rugged battery powered mobile printer which prints durable synthetic asset labels.

Long battery life and high impact resistance make it ideal for use in the field, whatever the environment.

It has a high speed processor and large memory for quick and efficient processing of complex labels, graphics and fonts using Bluetooth wireless technology.

Key Features

- Rugged Design
- Portable
- Long battery life

Supplied With

- Battery charger
- Battery pack
- Belt clip
- Label roll (approx. 180 off 52 x 74mm labels)

Labels

- Label roll with perforation (approx. 180 off 52 x 74mm labels) Part number: 339A041
- Label roll without perforation (approx. 160 off 52 x 74mm labels)

 Part number: 339A944
- Label roll. Only compatible with Apollo series testers (approx. 400 off 52 x 25mm labels)

 Part number: 339A945

Compatibility

- Apollo 600
- Apollo 500
- PrimeTest 350
- PrimeTest 300
- Supernova Elite (via serial cable)

Dimensions: (W x H x D) 112 x 173 x 74mm

Weight: 658g

Part number: 339A970

339A975 (with serial cable)



Tel: +44 (0) 191 587 8741 **Email:** sales@seaward.co.uk



Test n Tag Pro

An extremely lightweight and portable battery powered mobile printer.

The Test n Tag Pro prints durable synthetic asset labels which can include barcode, asset number, test date, next test date, user name and test status (dependent on which tester is being used).

It can be used with a rechargeable battery pack or primary cells and is ideal for use with the Apollo series testers via Bluetooth or PrimeTest 250+ via serial cable.

Key Features

- Lightweight and Portable
- Small 52 x 25mm labels available ideal for small areas such as plug tops
- Can be used with rechargeable battery pack or use primary cells

Supplied With

- Universal charger
- Battery pack
- Primary cell adapter
- Belt clip
- Serial connection cable (serial version only)
- Label roll with Bluetooth & serial version (approx. 400 off 52 x 25mm labels)
- Label roll with serial only version (approx. 160 off 52 x 74mm labels)

Labels

- Label roll (approx. 160 off 52 x 74mm labels) Part number: 339A944
- Label roll (approx. 400 off 52 x 25mm labels) Part number: 339A945

Compatibility

Bluetooth Connection

- Apollo 600
- Apollo 500

Serial Connection

PrimeTest 250+ (only with 52 x 25mm labels)

Dimensions: (W x H x D) 95 x 65 x 128mm

446g (including battery & full roll of paper)

Serial and Bluetooth Connection 339A980 Serial only connection 339A933



IMPORTANT INFORMATION: Please be aware that use of non-Seaward approved labels can prematurely wear the print heads and so will void your Seaward printer warranty.

www.seaward.co.uk

Tel: +44 (0) 191 587 8741 Email: sales@seaward.co.uk



Bluetooth Barcode Scanner

A portable asset label ID laser scanner with Bluetooth interface.

It is extremely compact and lightweight, making it ideal for mobile applications. USB rechargeable lithium-ion battery. Reads 1D barcode formats code 39, code 93 & code 128.



Key Features

- Lightweight & portable
- Wireless Bluetooth connectivity
- Compatible with Apollo series of testers

Compatibility

- Apollo 600
- Apollo 500
- PrimeTest 350
- PrimeTest 300

Dimensions: (W x H x D) 30 x 60 x 14mm

Weight: 30g

Part number: 339A923

CCD Barcode Scanner

A non contact barcode label scanner for rapid, error free entry of appliance number, test code and asset details.

Connects to Supernova Elite via serial connection. Reads 1D barcode formats code 39 & code 128.



Key Features

- Connects directly to the tester via serial cable
- Hand-held and easy to use
- Compatible with Supernova Elite and Europa Plus testers

Compatibility

- Supernova Elite
- Europa Plus

Dimensions: (W x H x D) 164 x 77.5 x 63mm

Weight: 160g (excluding lead)

Part number: 194A922

