

ABB WYLEX SALES LIMITED


CONTENTS

THE RANGE	PAGES 6 - 8
SWITCH FUSE - INSULATED	PAGE 6
Consumer Unit - D.P. Main Switch Isolator - Insul	ATED PAGE 6
SWITCH FUSE - METAL	PAGE 6
Consumer Unit - D.P. Main Switch Isolator - Metal	. PAGE 6
REWIRABLE FUSE ASSEMBLIES	PAGE 7
CARTRIDGE FUSE ASSEMBLIES	PAGE 7
PLUG-IN MCB ASSEMBLIES	PAGE 7
SPARE CARTRIDGE FUSE LINKS	PAGE 8
ACCESSORIES	PAGE 8
RCD RETROFIT KIT	PAGE 9
TECHNICAL DATA PA	GES 10 - 11

THE RANGE







The following Switch Fuses and Consumer Units are supplied without outgoing protective devices. Select from MCBs, cartridge fuse assemblies or rewirable fuse assemblies when ordering (See page 7). Units with incoming switch ratings of 100A have provision for one way rated above 32A.

SWITCH FUSE - INSULATED

RS CAT. NO.

rating	No. OF WAYS	CAT REF.
45A	1 199-3	925 104
60A	1 199-3	931 108
45A	1 199-2	8 <i>09</i> 145C*
60A	1 199-3	947 160C*

CONSUMER UNIT WITH D.P. MAIN SWITCH ISOLATOR -INSULATED

RATING	No. OF WAYS		CAT REF.
45A	2	199-3953	204
60A	3	199-3975	304
60A	4	199-2815	404
100A	6	199-3981	604
100A	8		804

SWITCH FUSE - METAL

rating	No. OF WAYS	CAT REF.
45A	1	106
60A	1	108M
45A	1	145CM*
60A	1	160CM*
80A	1	110M/80*
100A	1	110M*

CONSUMER UNIT WITH D.P. MAIN SWITCH ISOLATOR - METAL

RATING	No. OF WAYS	CAT REF
45A	2	206
· 45A	3	306
45A	4	406
100A	6	606
100A	8	806
100A	12	1206

^{*} These units are supplied fitted with the relevant cartridge fuse.

ABB WYLEX SALES LIMITED

THE RANGE




REWIRABLE FUSE ASSEMBLIES (Complete with contact shield) RS CAT ALC

		KJ CHI, NO	•
RATING	CONTACT SHIELD CO	OLOUR	CAT REF.
5A	WHITE	199-3997	R5
15A	BLUE	199-2821	R15
20A	YELLOW	199-4007	R20
30A	RED	199-2837	R30


CARTRIDGE FUSE ASSEMBLIES (Complete with contact shield)

RATING	CONTACT SHIELD CO	LOUR	CAT REF
5A	WHITE	199-2	843 C5
15A	BLUE	199-2	859 C15
20A	YELLOW	199-2	865 C20
30A	RED	199-2	871 C30
35A	ORANGE	199-4	013 C35
40A	ORANGE	199-2	887 C40
45A	GREEN	199-2	900 C45



CARTRIDGE FUSE ASSEMBLIES FOR 108 AND 108M


RATING	LABELS	CAT REF.
45A	-	199-2916 L45
60A	<u>-</u>	199-2922 L60



PLUG-IN MCB ASSEMBLIES (Complete with contact shield)

RATING	CONTACT SHIELD COLOUR		CAT REF.
6A	WHITE	199-4029	В6
10A	GREY	199-2938	B10
16A	BLUE	199-2944	B16
20A	YELLOW	199-2966	B20
32A	RED	199-2972	B32
40A	ORANGE	199-2988	B40


THE RANGE



INSULATED CONSUMER UNITS – PLUG-IN MCB RETROFIT APPLICATION GUIDE

In order to retrofit plug in MCBs the fuse cover of the consumer unit must be modified as shown in the diagram opposite. Alternatively a spare fuse cover may be selected from the list below.

RS V				RS CAT. No.
	OVER CAT REF. (C	Only ivory Size	colour available) Main Unit Type	
Fuse Cover	removed	5,20	7 ,	
A1866	A1866X	1 Way	104 Switch Fuse 45A	Max. 199-2994
A1861	A1861X	2 Way	204 Consumer Unit	199-3004
A1862	A1862X	3 Way	304 Consumer Unit	199-3010
A1863	A1863X	4 Way	404 Consumer Unit	199-3032
A1864	A1864X	6 Way	604 Consumer Unit	199-3048
A1865	A1865X	8 Way	804 Consumer Unit	



METAL CONSUMER UNITS – PLUG-IN MCB RETROFIT APPLICATION GUIDE

In order to retrofit plug in MCBs the fuse cover of the consumer unit must be modified as shown in the diagram opposite. Alternatively a spare fuse cover may be selected from the list below.

A1870	A1870X	4 Way	406/4106 Consumer Unit
A1869	A1869X Inclu	3 Way ding Lid Ins	306 Consumer Unit
A1868	A1868X	2 Way	206 Consumer Unit
A1873	A1873X	1 Way	106 Switch Fuse 45A Max
Standard Fuse Cover	with cut-out removed	Size	olour only available RAL7035 Main Unit Type