

Level Measurement

Continuous level measurement

Ultrasonic / Accessories for level sensors / EA aiming devices

Application

EA 304 aiming device

The Easy Aimer 304 flange is a stainless steel aiming device for alignment of Siemens level sensors used for level measurement of bulk solids.

The sensor must be mounted aimed towards the low level draw point in the silo. The sensor can be rotated through 360° and angled at 0 to 27° off vertical. It must be mounted using an access plate with welded studs or a flange in order to isolate the mounting holes from the pressurized environment. When installed properly, the EA 304 aiming device is capable of withstanding pressures up to 0.5 bar (Europe) or 15 psi (North America). It can even be used in corrosive and aggressive environments.

EA 2 aiming device

The Easy Aimer 2 flange is a cast aluminum aiming device for alignment of Siemens level sensors.


The flange has graduated adjustments and an adjustable insertion length. When used for applications with bulk solids, the sensor is mounted so that it is aimed towards the lower level draw point in the silo. The sensor can be rotated through 360° and angled at 0 to 20° off vertical. It must be mounted using an access plate with welded studs or a flange in order to isolate the mounting holes from the pressurized environment. When installed properly, the EA 2 aiming device is capable of withstanding pressures up to 0.5 bar (Europe) or 15 psi (North America). It can even be used in corrosive and aggressive environments.

Selection and ordering data

	Article No.
Easy aimer Used on solids applications to aim level sensors for optimal performance. Available in a 304 stainless steel model, or a cast aluminum model.	
Easy Aimer 2, aluminum with M20 adapter and 1" and 1½" BSPT aluminum couplings	7ML1830-1AX
Easy Aimer 304, with M20 adapter and 1" and 1½" BSPT 304 stainless steel couplings	7ML1830-1GN
Easy Aimer 2, aluminum, BSPT conduit	7ML1830-1AL
Easy Aimer 2, aluminum, NPT with 1½" galvanized coupling ¹⁾	7ML1830-1AN
Easy Aimer 2, aluminum, NPT with 1" galvanized coupling	7ML1830-1AP
Easy Aimer 2, aluminum, NPT with ¾" x 1" PVC coupling	7ML1830-1AQ
Easy Aimer 304, BSPT conduit	7ML1830-1AS
Easy Aimer 304, NPT with 1½" stainless steel coupling ¹⁾	7ML1830-1AT
Easy Aimer 304, NPT with 1" stainless steel coupling	7ML1830-1AU
Operating Instructions	
All literature is available to download for free, in a range of languages, at http://www.siemens.com/processinstrumentation/documentation	

¹⁾ For use with XPS-30 transducers only.

Dimensional drawings




EA 304 aiming device, dimensions in mm (inch)

Level Measurement

Continuous level measurement

Ultrasonic / Accessories for level sensors / EA aiming devices

Dimensional drawings (continued)



EA 2 aiming device, dimensions in mm (inch)