

Halogen Classic P45

Halogen Classic 28W E27 240V P45 1CT

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

• General Characteristics

Cap-Base	ES [ES]
Bulb	P45 [P 45mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Life to 50% failures	2000 hr
Nominal Lifetime	2000 hr
Rated Lifetime	2000 hr
Rated Lifetime (years)	2 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2800 K
Colour Temperature Technical	2800 K
Lamp Luminous Flux	370 Lm
Rated Luminous Flux	370 Lm
Lamp Luminous Efficacy	12.4 Lm/W
LLMF - end nominal lifetime	80 (min) %

• Electrical Characteristics

Rated Wattage	28.0 W
Lamp Wattage	28 W
Technical Lamp Power	28 W
Power Factor	1 -
Voltage	240 V
Lamp Current	0.12 A
Dimmable	yes
Wattage Equivalent	35 W
Starting Time	0.0 s

Warm-up Time to 60% Light Outp	instant full light
--------------------------------	--------------------

• Environmental Characteristics

Energy Efficiency Label (EEL)	D
Energy consumption kWh/1000h	28 kWh

• Measuring Conditions

Switching cycle	8000X
-----------------	-------

• Luminaire Design Requirements

Cap-Base Temperature	130 (max) C
----------------------	-------------

• Product Dimensions

Overall Length C	74 (max) mm
Diameter D	46 (max) mm

• Product Data

Order code	863000 04
Full product code	872790086300004
Full product name	Halogen Classic 28W E27 240V P45 1CT
Order product name	Halogen Classic 28W E27 240V P45 1CT/15
Pieces per pack	1
Packing configuration	15
Packs per outerbox	15
Bar code on pack - EAN1	8727900863000

PHILIPS


Halogen Classic P45

Bar code on
outerbox - EAN3
Logistic code(s) -
12NC

8718696462539
925647445506

Net weight per piece 19.300 gr

Dimensional drawing



E27

Halogen Classic 28W E27 240V P45 1CT

Product	C (Max)	D (Max)
HalClass 28W E27 240V P45 CL	74	46



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, September 24
data subject to change