

Hynit®

32-105

Oil-repellent glove protecting from oil, grease and dirt



Oil



Light Duty

Lightweight protective gloves affording durability, flexibility and comfort

- **Improved durability and flexibility:** Hynit® 32-105 industrial gloves feature a special nitrile formulation that combines excellent abrasion resistance with superb flexibility
- **Increased protection:** These hand protection gloves' liquid-repellent impregnation repels oil, grease and dirt
- **Elevated comfort:** As these durable work gloves are made from cotton, they ensure breathability and comfort



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Mining

Applications

- Assembly & inspection of components
- Delivery of parts to production line
- Seizing structural parts
- Loading and unloading rough parts or boxes
- Final assembly
- Handling application & cleaning tools
- Shipping and loading of product



32-105

Oil-repellent glove protecting from oil, grease and dirt

Key Features

- **Special nitrile formulation:** Excellent durability and flexibility
- **Liquid-repellent impregnation:** Resists oil, grease and dirt
- **Interlock knit liner:** Ensures breathable comfort

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



3111A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
Hynit® 32-105	Finishing: Fully Impregnated Coating Material: Nitrile Liner Material: Cotton, Interlock knit Cuff Style: Slip-on	N/A	6.5, 7, 7.5, 8, 9, 10	208-237 mm/ 8.18-9.33 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

