



1/4" & 1/2" SOCKET SET 93 PIECES

- 93-piece 1/4" & 1/2" socket set for automotive and workshop tasks
- Hard-wearing carry case
- Integrated carry handle moulded directly into the case
- Metal latch mechanisms
- Metal hinge pins
- Fully organised layout with dedicated positions for all tools
- Moulded tool size markings
- DIN & ISO standard tools

The TengTools TMN093 is a 93-piece 1/4" and 1/2" socket set. The low-profile carrying case features a red hard-shell body made from hard-wearing, impact-resistant PE-HD. The TengTools wordmark is embossed on the front. An integrated carry handle is moulded directly into the top of the case. Metal latch mechanisms sit along the front edge of the lid. The rear of the case uses metal hinge pins. Moulded size markings beside each tool position make it easy to identify the correct tool. The lid half holds a spark plug socket, extension bars, adaptors, a set of combination spanners, and deep sockets. The base half houses ratchets, socket sets, a bit and driver assortment, a spinner handle, and adaptors/couplers. The tools are manufactured to DIN and ISO standards, conforming to internationally recognised sizing and tolerance specifications.

General information

Country of origin: Taiwan
Barcode: 5020385305298
Tariff code Europe: 8204200000
ECCN EU: NOCLASS
ECCN US: EAR99
ETIM: EC000149
UNSPSC: 27111703

Attributes

Product type: General Tool Sets, Sockets & Accessories Sets, Spanners & Wrench Sets
Number of pieces: 93
Drive: 1/4", 1/2", 1/4" Hex
Socket type: Regular, Deep
Measuring system: Metric

Dimensions

Item weight (g): 5392
Width (mm): 470
Depth (mm): 260
Height (mm): 104

Technical changes and errors may occur. 04-08-2026 09:25

DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



William Gibsons väg 1A
 433 76 Jonsered,
 Sweden



WWW.TENGTOOLS.COM



WWW.TENGTOOLS.COM

1200FRP	1/2" Ratchet FRP 45 Teeth
1400FRP	1/4" Ratchet FRP 45 Teeth
220745	TX Bits 40 mm TX45
220750	TX Bits 40 mm TX50
220760	TX Bits 40 mm TX60
310502	Hex Key Metric 2 mm
600508	Combination Spanner Metric 8 mm
600509	Combination Spanner Metric 9 mm
600510	Combination Spanner Metric 10 mm
600511	Combination Spanner Metric 11 mm
600512	Combination Spanner Metric 12 mm
600513	Combination Spanner Metric 13 mm
600514	Combination Spanner Metric 14 mm
600515	Combination Spanner Metric 15 mm
600517	Combination Spanner Metric 17 mm
600519	Combination Spanner Metric 19 mm
3105015	Hex Key Metric 1.5 mm
3105025	Hex Key Metric 2.5 mm
ACC50MBH01	1/4" Magnetic Bit Holder 50 mm
ACCSDA1412	1/4" Hex drive impact socket adaptor for 1/2" sockets
ACCSDA1414	1/4" Hex drive impact socket adaptor for 1/4" sockets
FL2507A03	1/4" Flat Bits 25 mm 7 mm
FL2508A03	1/4" Flat Bits 25 mm 0.8 × 4.0 mm
FL2508B03	1/4" Flat Bits 25 mm 0.8 × 5.5 mm
HEX2500303	1/4" Hex Bits 25 mm 3 mm
HEX2500403	1/4" Hex Bits 25 mm 4 mm

HEX2500503	1/4" Hex Bits 25 mm 5 mm
HEX2500603	1/4" Hex Bits 25 mm 6 mm
HEX2500803	1/4" Hex Bits 25 mm 8 mm
HEX2501003	1/4" Hex Bits 25 mm 10 mm
M120021-C	1/2" Extension Bar 125 mm
M120022-C	1/2" Extension Bar 255 mm
M120030-C	1/2" Universal Joint
M120046-C	1/2" Spark Plug Socket 21 mm
M120061-C	1/2" Bit Adaptor 10 mm
M120062-C	1/2" Bit Adaptor 12 mm
M140015-C	1/4" Spinner Handle
M140020-C	1/4" Extension Bar 50 mm
M140021-C	1/4" Extension Bar 100 mm
M140030-C	1/4" Universal Joint
M140050-C	1/4" Sliding T Bar
M140060-C	1/4" Bit Adaptor Hex Bit Coupler
M140504-C	1/4" Socket 6 pt Metric 4 mm
M140505-C	1/4" Socket 6 pt Metric 5 mm
M140506-C	1/4" Socket 6 pt Metric 6 mm
M140507-C	1/4" Socket 6 pt Metric 7 mm
M140508-C	1/4" Socket 6 pt Metric 8 mm
M140509-C	1/4" Socket 6 pt Metric 9 mm
M140510-C	1/4" Socket 6 pt Metric 10 mm
M140511-C	1/4" Socket 6 pt Metric 11 mm
M140512-C	1/4" Socket 6 pt Metric 12 mm
M140513-C	1/4" Socket 6 pt Metric 13 mm
M140604-C	1/4" Deep Socket 6 pt Metric 4 mm
M140605-C	1/4" Deep Socket 6 pt Metric 5 mm
M140606-C	1/4" Deep Socket 6 pt Metric 6 mm
M140607-C	1/4" Deep Socket 6 pt Metric 7 mm
M140608-C	1/4" Deep Socket 6 pt Metric 8 mm
M140609-C	1/4" Deep Socket 6 pt Metric 9 mm
M140610-C	1/4" Deep Socket 6 pt Metric 10 mm
M140611-C	1/4" Deep Socket 6 pt Metric 11 mm
M140612-C	1/4" Deep Socket 6 pt Metric 12 mm
M140613-C	1/4" Deep Socket 6 pt Metric 13 mm
M380036-C	Step Up Adaptor 3/8"F - 1/2"M
M1205106-C	1/2" Socket 6 pt Metric 10 mm
M1205116-C	1/2" Socket 6 pt Metric 11 mm
M1205126-C	1/2" Socket 6 pt Metric 12 mm
M1205136-C	1/2" Socket 6 pt Metric 13 mm
M1205146-C	1/2" Socket 6 pt Metric 14 mm
M1205156-C	1/2" Socket 6 pt Metric 15 mm
M1205176-C	1/2" Socket 6 pt Metric 17 mm
M1205196-C	1/2" Socket 6 pt Metric 19 mm
M1205206-C	1/2" Socket 6 pt Metric 20 mm
M1205246-C	1/2" Socket 6 pt Metric 24 mm
M1205276-C	1/2" Socket 6 pt Metric 27 mm
M1205306-C	1/2" Socket 6 pt Metric 30 mm
M1205326-C	1/2" Socket 6 pt Metric 32 mm
M1405045-C	1/4" Socket 6 pt Metric 4.5 mm
M1405055-C	1/4" Socket 6 pt Metric 5.5 mm
PH2500003	1/4" PH Bits 25 mm PH0
PH2500103	1/4" PH Bits 25 mm PH1
PH2500203	1/4" PH Bits 25 mm PH2
PH2500303	1/4" PH Bits 25 mm PH3

PZ2500103	1/4" PZ Bits 25 mm PZ1
PZ2500203	1/4" PZ Bits 25 mm PZ2
PZ2500303	1/4" PZ Bits 25 mm PZ3
TX2500803	1/4" TX Bits 25 mm TX8
TX2501003	1/4" TX Bits 25 mm TX10
TX2501503	1/4" TX Bits 25 mm TX15
TX2502003	1/4" TX Bits 25 mm TX20
TX2502503	1/4" TX Bits 25 mm TX25
TX2502703	1/4" TX Bits 25 mm TX27
TX2503003	1/4" TX Bits 25 mm TX30
TX2504003	1/4" TX Bits 25 mm TX40