

Portable 4 Port SuperSpeed Mini USB 3.0 Hub - White

Product ID: ST4300MINU3W



The ST4300MINU3W Portable 4 Port SuperSpeed Mini USB 3.0 Hub (White) lets you expand your USB connectivity by turning a single USB 3.0 port into four external USB 3.0 ports. The integrated cable design makes this mini USB hub the perfect accessory for your Mac® / PC notebook or Ultrabook™ computer.

The 4 Port USB 3.0 hub supports USB 3.0 data bandwidth (5 Gbps - up to 10x more than USB 2.0) and is backward compatible with USB 2.0 and 1.1 devices, ensuring flawless performance from all of your USB peripherals/devices, regardless of their age.

Ideal for home and business users who require portability, the external USB 3.0 hub is USB-powered and features a rugged, compact design with a built-in cable so no additional cables are needed to connect the hub to your system.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mac or PC notebook / Ultrabook™ users with limited USB 3.0 ports and multiple USB 3.0 devices
- Make hard to access USB ports more accessible, by being able to position the hub anywhere the cable will reach
- Separate tightly packed USB ports, to better accommodate larger USB plugs or prevent overcrowding

Features

- Four USB type-A ports that can be accessed simultaneously
- SuperSpeed USB 3.0 compliant, with data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.0/1.1 specifications and devices
- Compact and portable design with built-in cable
- Plug-and-Play and hot-swap compatible

Hardware	Warranty	2 Years
	Bus Type	USB 3.0
	Chipset ID	Genesys Logic - GL3522
	Fast-Charge Port(s)	No
	Interface	USB 3.0
	Ports	4
	USB-C Device Port(s)	No
	USB-C Host Connection	No
Performance	Maximum Data Transfer Rate	5 Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	External Ports	1 - USB Type-A (9 pin) USB 3.0 Male 4 - USB Type-A (9 pin) USB 3.0 Female
	OS Compatibility	OS Independent; No additional drivers or software required
Special Notes / Requirements	System and Cable Requirements	Available USB Port
Indicators	LED Indicators	1 - Power
Power	Power Source	USB-Powered
Environmental	Humidity	0~80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	5.7 in [145 mm]
	Color	White
	Enclosure Type	Plastic
	Form Factor	Compact
	Product Height	0.6 in [14 mm]
	Product Length	3.1 in [80 mm]
	Product Weight	1.3 oz [38 g]
	Product Width	1.4 in [36 mm]
Packaging Information	Shipping (Package) Weight	3.8 oz [109 g]
What's in the Box	Included in Package	1 - USB 3.0 hub 1 - quick-start guide

Product appearance and specifications are subject to change without notice.