

A360 - Senti - Flex Glove

Collection: General Handling

Range: Hand Protection

Materials: Nylon, Elastic, Polyester

Dipping:

Inner Pack: 12

Outer Carton: 480

Product information

The ultra thin 18 gauge glove for the ultimate in dexterity and breathability. The PU dip allows for a level 3 abrasion resistance. The elasticated cuff ensures a comfortable and secure fit.

General Handling

The general handling and grip glove category is one of the most popular collections within the Portwest hand protection range. A carefully selected range of coatings, including latex, nitrile, polyurethane and PVC, provides a broad range of styles suited to a diverse range of tasks.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (3121X)



Features

- Smooth PU coating for increased abrasion resistance
- 18 gauge liner provides excellent comfort, freedom of movement and superb tactile ability
- Low linting construction for minimal contamination
- Breathable seamless liner
- Elasticated cuffs for a secure fit
- Lightweight and comfortable
- CE certified
- Retail tag which aids presentation for retail sales



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A360 - Senti - Flex Glove Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/18553-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
SATRA Technology Park
NN16 8SD, United Kingdom
Cert No: AB0321/19085-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A310GRWXS	Grey/White	60.0	26.0	53.0	0.0320	0.0827	5036108290420	25036108780659
A310GRWS	Grey/White	60.0	26.0	53.0	0.0360	0.0827	5036108203673	25036108696080
A310GRWM	Grey/White	60.0	26.0	53.0	0.0410	0.0827	5036108174768	25036108674125
A310GRWL	Grey/White	60.0	26.0	53.0	0.0440	0.0827	5036108174751	25036108674118
A310GRWXL	Grey/White	60.0	26.0	53.0	0.0460	0.0827	5036108174775	25036108674132
A310GRWXXL	Grey/White	60.0	26.0	53.0	0.0470	0.0827	5036108261963	25036108674149