

## USB-C to USB-C Cable w/ 5A PD - M/M - 0.5 m - USB 2.0 - USB-IF Certified

Product ID: USB2C5C50CM



With up to 5A (100W) of power output, you can use this USB-C™ to USB-C cable to power and charge a USB-C laptop, such as your Apple MacBook Pro, MacBook or Chromebook Pixel™, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

### Fast-charge your mobile devices

The 5A of Power Delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable, which is perfect for people on the move. Decrease your charge times and make sure your mobile devices are ready, whenever you need them while you're on the road.

The short cable lets you set up in small offsite workspaces, or in a coffee shop or hotel room. You can connect a mobile device such as your phone or tablet to your laptop without excess cable getting in your way.

## **Provide superior connections with USB-IF certified cables**

The USB Type-C cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB2C5C50CM from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Power your USB-C laptop from a charger or power bank
- Charge your USB-C laptop from a docking station
- Fast-charge your USB-C mobile devices from a charger
- Sync your USB-C mobile devices with a laptop

### Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Thunderbolt™ 3 port compatible
- Guaranteed reliability with our 2-year warranty

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps) Male
	Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps) Male
<b>Power</b>	Power Delivery	100W
<b>Physical Characteristics</b>	Cable Length	1.6 ft [0.5 m]
	Color	Black
	Connector Style	Straight
	Product Height	0.2 in [0.6 cm]
	Product Length	1.6 ft [0.5 m]
	Product Width	0.4 in [10 mm]
	Weight of Product	1 oz [29 g]
	Wire Gauge	24/26 AWG
<b>Packaging Information</b>	Package Height	0.4 in [10 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	1.2 oz [34 g]
<b>What's in the Box</b>	Included in Package	1 - USB-C cable

Product appearance and specifications are subject to change without notice.