




3C-SCREWDRIVER WITH STRIKING CAP

2154SK

3C-SCREWDRIVER WITH STRIKING CAP for slotted head screws

- Acc. to DIN ISO 2380-2, blade tip acc. to DIN ISO 2380-1 Form A
- 3-component handles Power-Grip³ with striking cap
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Hexagon blade with additional hexagon bolster
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel



mm	mm	mm	mm	mm	mm	mm	Code	No.
3.5	0.6	75	180	8	0.086		1845209	2154SK 3,5
4.5	0.8	75	180	8	0.090		1845217	2154SK 4,5
5.5	1.0	100	205	8	0.092		1845225	2154SK 5,5
6.5	1.2	125	230	10	0.154		1845233	2154SK 6,5
6.5	1.2	150	255	10	0.229		2824108	2154SK 6,5-150
7.0	1.2	125	230	10	0.229		2824116	2154SK 7
8.0	1.2	150	270	13	0.178		1845241	2154SK 8
8.0	1.6	175	295	13	0.229		2824124	2154SK 8-175
10.0	1.6	200	320	13	0.214		1845268	2154SK 10
10.0	1.6	300	420	13	0.229		2824132	2154SK 10-300
12.0	2.0	200	320	16	0.260		1845276	2154SK 12
12.0	2.0	250	370	16	0.229		2824140	2154SK 12-250
14.0	2.5	250	370	16	0.324		1845284	2154SK 14

2160SK PZ

3C-SCREWDRIVER WITH STRIKING CAP for cross-head screws Pozi PZ

- Acc. to DIN ISO 8764, tip acc. to DIN ISO 8764-1 PZ
- 3-component handles Power-Grip³ with striking cap
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Hexagon blade with additional hexagon bolster
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel




PZ	mm	mm	mm	mm	mm	mm	Code	No.
1	M2 - M3	80	185	8	0.086		1845330	2160SK PZ 1
2	M3,5 - M5	100	205	10	0.148		1845349	2160SK PZ 2
3	M5,5 - M7	150	270	13	0.206		1845357	2160SK PZ 3



SK 2154 PH-06

3C-SCREWDRIVER SET WITH STRIKING CAP 6 pieces

- Practical set composition in environmentally-friendly cardboard box
- For firmly seated slotted and cross-head screws PH
- Hexagon blade with additional hexagon bolster
- 3-component handles Power-Grip³ with striking cap
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel



Contents	mm	Code	No.
2154SK 4,5 5,5 6,5 8	0.880	1878743	SK 2154 PH-06
2160SK PH 1 2			

2160SK PH

3C-SCREWDRIVER WITH STRIKING CAP for cross-head screws PH

- Acc. to DIN ISO 8764, tip acc. to DIN ISO 8764-1 PH
- 3-component handles Power-Grip³ with striking cap
- Ergonomic handle design enables precise and fatigue-free working
- Positive-fit joint of handle and blade for optimum transmission of force
- Hexagon blade with additional hexagon bolster
- Blade from GEDORE molybdenum-vanadium-Plus tempered steel



PH	mm	mm	mm	mm	mm	Code	No.
1	M2 - M3	80	185	8	0.086	1845292	2160SK PH 1
2	M3,5 - M5	100	205	10	0.148	1845306	2160SK PH 2
3	M5,5 - M7	150	270	13	0.204	1845314	2160SK PH 3