

CorePro LEDbulb

CorePro LEDbulb 10.5-75W E27 830

Delivering a warm, halogen-like accent beam, LEDspots are a perfect fit for spot lighting and have a broad compatibility with transformers. LEDspots are compatible with most existing fixtures with a GU10 / MR16 GU5.3 / E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs. LEDcandle and LEDluster are compatible with existing fixtures with an E27/E14 holder and are designed for retrofit replacement of incandescent lamps. LEDlamps deliver huge energy savings and minimize maintenance cost

Product data

• General Characteristics

Cap-Base	ES
Bulb	A60 [A 60mm]
Rated Lifetime	15000 hr
Nominal Lifetime hours	15000 hr

• Light Technical Characteristics

Colour Code	830
Colour Designation	White
Correlated Colour Temperature	3000 K
Luminous Flux	1055 Lm
Colour rendering index	80
Luminous Efficacy Lamp	100.48 Lm/W
Colour Temperature	3000 K [CCT 3000K]
Rated Luminous Flux	1055 Lm
LLMF - end nominal lifetime	70 %
Colour consistency	6 steps

• Electrical Characteristics

Wattage	10.5 W
Voltage	220-240 V
Line Frequency	50-60 Hz
Power Factor	0.5 -
Lamp Current mA	95 mA
Dimmable	No
Wattage Equivalent	75 W
Rated Wattage	10.5 W
Starting Time	0.5 (max) s
Warm-up Time to 60% Light Outp	instant full light

Suitable for accent lighting No

• Temperature Characteristics

T-case maximum 95 C

• Environmental characteristics

Energy Efficiency Label (EEL) A+
Energy consumption kWh/1000h 13 kWh

• Measuring Conditions

Switching cycle 50000X

• Product Dimensions

Overall Length C 102.6 mm
Diameter D 56.3 mm

• Product Data

Order code 414866 00
Full product code 871869641486600
Full product name CorePro LEDbulb 10.5-75W E27 830
Order product name CorePro LEDbulb 10.5-75W E27 830
Pieces per pack 1
Packing configuration 6
Packs per outerbox 6
Bar code on pack - EAN1 8718696414866
Bar code on outerbox - EAN3 8718696414873




PHILIPS

CorePro LEDbulb

Logistic code(s) - 929000249462
12NC

Net weight per piece 0.081 kg

Dimensional drawing




CorePro LEDbulb 10.5-75W E27 830

Product	C (Norm)	D (Norm)
LED 10.5-75W E27 830 220-240V A60	102.6	56.3



E27

Photometric data



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, June 18
data subject to change