



 PRODUCT-DETAILS

2601/7 WDI

Switch Rocker/button, Intermediate switch with Not included blue - Busch-Duro 2000 WDI



General Information

Extended Product Type	2601/7 WDI
Product ID	2CKA001084A0805
EAN	4011395026601
Catalog Description	Switch Rocker/button, Intermediate switch with Not included blue - Busch-Duro 2000 WDI
Long Description	For difficult on-site conditions such as aggressive media (ammonia, petrol, oils, greases, cleaning agents in usual concentrations) we recommend the use of cable entries 2070/2071.

Installation

Instructions and Manuals	No document needed
Mounting Type	Surface Mounted
Type of Fastening	Mounting with Screw
Modular Components Included	Complete Device

Environmental

Degree of Protection	IP66
----------------------	------

Technical

Data Sheet, Technical Information	No document needed
Function	Function lighting: Control and orientation
Number of Rocker Switches	1
Wiring Configuration	Intermediate switch
Actuator Type	Rocker/button
Lamp Type	Not included
Illumination	Optional
Terminal Type	Screwless Terminals

Electrical

Rated Voltage (U_r)	250 V
Rated Current (I_n)	16 A
Power Watt	LEDi / CFLi 200 W

Design

Design Range	Busch-Duro 2000 WDI
Surface Finishing	Untreated Matt
Material	Thermoplastic
Label Space Provided	Without Label Space
RAL Number	Similar to RAL 5010
Color	blue

Dimensions

Product Net Width	74 mm
Product Net Height	93 mm
Product Net Depth / Length	54 mm
Product Net Weight	160 g
Dimension Diagram	2CKA000097E0614

Material Compliance

RoHS Declaration	2CKA200000E0288
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Declaration	2CKA309999E9999
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20250901
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany

Simplified SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer

Certificates and Declarations

Declaration of Conformity - CE	2CKA100000E0190
EU Data Act Applicability and Compliance	Not Applicable

External Classifications and Standards

ETIM 9	EC001590 - Installation switch
ETIM 10	EC001590 - Installation switch
eClass	V11.0 : 27144053

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CKA001716A0042	Mounting Plate 1-gang brass	2609 WS	1	piece
2CKA001714A0229	Symbol for rocker with Symbol "bell" transparent	2145 KI	1	piece
2CKA001714A0211	Symbol for rocker with Symbol "light" transparent	2145 LI	1	piece
2CKA001714A0203	Symbol for rocker with Neutral symbol transparent	2145 N	1	piece
2CKA001714A0237	Symbol for rocker with Symbol "key" transparent	2145 TR	1	piece
2CKA001714A0245	Symbol for rocker with Neutral symbol red transparent	2145-12	1	piece
2CKA001784A0016	Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V	8332-1	1	piece
2CKA001784A0024	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 3 ... 8 V	8333-1	1	piece
2CKA001784A0529	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 12 V	8335-1	1	piece
2CKA001784A0040	Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V	8339-1	2	piece
2CKA001784A0321	Illumination set for Switch/push button Orange Neon lamp, 1 mA, 230 V	8346-1	1	piece
2CKA001784A0719	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 24 V AC/DC	8358	1	piece
2CKA001761A0808	Cable Entry blue	2081	1	piece
2CKA001761A0782	Cable Entry blue	2079	1	piece
2CKA001761A1368	Cable Entry grey	2070	1	piece
2CKA001761A1376	Cable Entry grey	2071	1	piece

Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Surface Mounted Range → Mechanical Controls

