



**Part Number :** 469931010

**Product Description :** Mini-Fit Jr. Plug Housing, Dual Row with Panel Mount Ears, Nylon 6/6, UL 94V-2, Panel Mount, 10 Circuits, Glow-Wire Capable, Black

**Series Number :** 46993

**Status :** Active

**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[469931010\\_sd.pdf](#)

### 3D Models and Design Files

[469931010\\_stp.zip](#)

### Specifications

[55560001-AS-000.pdf](#)

[55560002-AS-000.pdf](#)

[PK-5559-001-001.pdf](#)

[PS-45750-001-001.pdf](#)

[PS-5556-001-001.pdf](#)

[457500003-TS-000.pdf](#)

[55560001-TS-000.pdf](#)

[55560010-TS-000.pdf](#)

[TS-5556-002-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	46993
Description	Mini-Fit Jr. Plug Housing, Dual Row with Panel Mount Ears, Nylon 6/6, UL 94V-2, Panel Mount, 10 Circuits, Glow-Wire Capable, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Mini-Fit Jr.
UPC	887191639123

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	10
--------------------	----

Color - Resin	Black
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.660/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Dual Row Receptacle Housings	<u>46992</u>

### Use with Part(s)

Description	Part Number
Mini-Fit Male Crimp Terminals	<u>5558</u>
Mini-Fit Plus Male Crimp Terminals	<u>46012</u>