## **RS Pro 16mm IP67 Push-Pull Connectors**



Cable-Mount Connector					In-Line Cable Connector (includes Dust Cap)					Rear-Nut Panel-Mount Connector (includes Dust Cap)				Square Flange Panel-Mount Connector (includes Dust Cap)		
RS Stock No:	No. of Contacts	For Cable Diameter	Gender		RS Stock No:	No. of Contacts	For Cable Diameter	Gender		RS Stock No:	No. of Contacts	Gender		RS Stock No:	No. of Contacts	Gender
206-5063	2	5.0 - 8.0mm	Female	Mates with	206-5072	2	5.0 - 8.0mm	Male	Or	206-5086	2	Male	Or	206-5103	2	Male
206-5064	3	5.0 - 8.0mm	Female	"	206-5073	3	5.0 - 8.0mm	Male	"	206-5088	3	Male	"	206-5104	3	Male
206-5066	4	5.0 - 8.0mm	Female	"	206-5074	4	5.0 - 8.0mm	Male	"	206-5089	4	Male	"	206-5105	4	Male
206-5067	5	5.0 - 8.0mm	Female	"	206-5075	5	5.0 - 8.0mm	Male	"	206-5090	5	Male	"	206-5106	5	Male
206-5068	7	8.0 - 12mm	Female	"	206-5076	7	8.0 - 12mm	Male	"	206-5091	7	Male	"	206-5107	7	Male
206-5069	9	8.0 - 12mm	Female	"	206-5077	9	8.0 - 12mm	Male	"	206-5092	9	Male	"	206-5108	9	Male
206-5062	10	8.0 - 12mm	Female	"	206-5070	10	8.0 - 12mm	Male	=	206-5085	10	Male	"	206-5102	10	Male
206-5055	2	5.0 - 8.0mm	Male	Mates with	206-5079	2	5.0 - 8.0mm	Female	Or	206-5095	2	Female	Or	206-5110	2	Female
206-5056	3	5.0 - 8.0mm	Male	"	206-5080	3	5.0 - 8.0mm	Female	"	206-5096	3	Female	"	206-5111	3	Female
206-5057	4	5.0 - 8.0mm	Male	"	206-5081	4	5.0 - 8.0mm	Female	"	206-5097	4	Female	"	206-5112	4	Female
206-5058	5	5.0 - 8.0mm	Male	"	206-5082	5	5.0 - 8.0mm	Female	"	206-5098	5	Female	"	206-5113	5	Female
206-5060	7	8.0 - 12mm	Male	11	206-5083	7	8.0 - 12mm	Female	"	206-5099	7	Female	"	206-5114	7	Female
206-5061	9	8.0 - 12mm	Male	"	206-5084	9	8.0 - 12mm	Female	"	206-5101	9	Female	"	206-5115	9	Female
206-5054	10	8.0 - 12mm	Male	"	206-5078	10	8.0 - 12mm	Female	"	206-5094	10	Female	"	206-5109	10	Female