

FEATURES

- Ergonomic multi-component handles
- Optimum balance of torque and control
- High quality
- Sturdy tool box

RS PRO 82 Piece Mechanical Tool Kit with Box

RS Stock No.: 136-3412



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO high quality 82 piece 1/2in socket and hand tool set is ideal for mechanics. This tool kit offers various tools carefully chosen to make one comprehensive kit, ideal for DIY or professional user. Supplied with a tool box to keep your tools safe, organised and secured. The kit includes an essential and useful selection of screwdrivers, sockets, spanners and pliers plus much more. The tools are strong and built to provide years of service.

General Specifications

Set Type	Mechanical
Set Contents	Chisel, Cutters, Feeler Gauges, Hammer, Hex Keys, Knife, Pliers, Punch, Ratchet, Screwdriver, Sockets, Spanners, Tape Measure, Voltage Tester
Number of Pieces	82
Storage Type	Box
Applications	Repair, Maintenance, DIY projects

Kit Contains

Name
Flat Chisel 21 x 150mm
Centre Punch: 4 x 120mm
Parallel Pin Punch 3mm, 4mm, 5mm, 6mm x 150mm
Soft Face Hammers
Ball Pein Hammer; 16 oz.
Stainless Steel Rules; 30mm
Water Pump Pliers (Box Joint/PVC); 250mm
Compact Tape Measure; 3 x 16mm
Feeler Gauge (Metric); 0.05 to 1.00mm
Trimming Knife
Double Open-End Wrench; 5 x 5.5mm, 6 x 7mm, 8 x 10mm
12 Piece Combination Wrench Set
1/2 inch Dr. 6-Point Sockets; 18 pieces plus 4 Accessories
1/2 inch Dr. Quick Release Reversible Ratchet
1/2 inch Dr. Sliding T-Handles
1/2 inch Dr. Extension Bar; 125mm
1/2 inch Dr. Extension Bar; 250mm
1/2 inch Dr. Universal Joint
18 Piece Hexagon L Key Set - Metric / Imperial
Long Nose Pliers; 160mm
Diagonal Cutter; 160mm
Combination Pliers; 180mm
Pozidriv Screwdriver; PZ1 x 80mm, PZ2 x 100mm
Slotted Screwdriver; 4.0 x 100mm, 5.5 x 125mm, 6.5 x 150mm, 8.0 x 150mm
Single-Pole Voltage Tester (Short)
Stubby Slotted Screwdriver; 5.5 x 25mm
Stubby Pozidriv Screwdriver; PZ2 x 25mm
Padlock

Approvals

VDE/1000V Approved	No
--------------------	----

