



4880 XM screwdriver Slotted

Item Number	Ø	→	↻	→
T4880X 08	2.5mm 3/32"	60mm 2 3/8"	0.20mm 0.008"	97mm 3 13/16"
T4880X 12	2.5mm 3/32"	60mm 2 3/8"	0.20mm 0.008"	97mm 3 13/16"
T4880X 15	2.5mm 3/32"	60mm 2 3/8"	0.25mm 0.010"	97mm 3 13/16"
T4880X 18	2.5mm 3/32"	60mm 2 3/8"	0.30mm 0.012"	97mm 3 13/16"
T4880X 256	2.5mm 3/32"	60mm 2 3/8"	0.40mm 0.016"	97mm 3 13/16"
T4880X 257	2.5mm 3/32"	75mm 3"	0.40mm 0.016"	97mm 3 13/16"
T4880X 310	3.0mm 1/8"	100mm 4"	0.50mm 0.020"	97mm 3 13/16"
T4880X 315	3.0mm 1/8"	150mm 6"	0.50mm 0.020"	97mm 3 13/16"
T4880X 324	3.0mm 1/8"	240mm 9 1/2"	0.50mm 0.020"	97mm 3 13/16"
T4880X 410	4.0mm 5/32"	100mm 4"	0.80mm 0.031"	97mm 3 13/16"
T4880X 415	4.0mm 5/32"	150mm 4"	0.80mm 0.031"	97mm 3 13/16"
T4880X 452	4.5mm 11/64"	250mm 10"	0.80mm 0.031"	97mm 3 13/16"



4880 XM screwdriver set

Item Number	i
T4880X/5	screwdriver set

Set of 5 Precision Screwdrivers in a presentation box. Containing one of each of slotted 2.5 x 75, 3.0 x 100, 4.0 x 100, PH 00 x 60, PH 0 x 60.

Order Online
www.carlkammerling.com



4877 XM screwdriver Torx

Item Number	i	Ø	→	→
T4877X 04	T 04	2.5mm 3/32"	50mm 2"	97mm 3 13/16"
T4877X 05	T 05	2.5mm 3/32"	50mm 2"	97mm 3 13/16"
T4877X 06	T 06	3.5mm 9/64"	50mm 2"	97mm 3 13/16"
T4877X 07	T 07	3.5mm 9/64"	50mm 2"	97mm 3 13/16"
T4877X 08	T 08	3.5mm 9/64"	60mm 2 3/8"	97mm 3 13/16"
T4877X 09	T 09	4.0mm 5/32"	60mm 2 3/8"	97mm 3 13/16"
T4877X 10	T 10	4.0mm 5/32"	80mm 3 1/8"	97mm 3 13/16"
T4877X 15	T 15	4.0mm 5/32"	80mm 3 1/8"	97mm 3 13/16"



4883 XM screwdriver set

Item Number	i
T4883X	7 piece screwdriver set

Set of 7 Precision screwdrivers. Containing one of each of T4880X 2.5 x 75, 3.0 x 100, 3.0 x 150, 4.0 x 150mm Slotted. T4882 Ph 0 x 60, 1 x 80mm Phillips.



4884 XM screwdriver set

Item Number	i
T4884X	4 piece screwdriver set

Set of 4 Precision screwdrivers. Containing one of each of T4880X 1.5 x 60, 2.5 x 75, 3.0 x 100mm Slotted. T4882 Ph 0 x 60mm Phillips.



4852 Watchmaker's screwdriver set of 4

Item Number	i
T4852P	4 piece screwdriver set

Contains slotted 1, 2, 3 and 4.



4854 Watchmaker's screwdriver set of 6

Item Number	i
T4854P	6 piece screwdriver set

Contains slotted 1, 2, 3 and 5, and PH 00 and 0.



4896 Multi-blade screwdriver set of 7

Item Number	i
T4896P	7 piece screwdriver set

Containing one of each 1.5, 2, 3 and 4mm Slotted and PH 000, 00, 0 and Torx 05, 06, 07, 08.



4826 Bit and Socket set

Item Number	i
T4826D	display packed

46 pc ratchet screwdriver, bit and socket set. Screwdriver style driver with a hi-torque ratchet. Magnetised shaft holds bits. Cushion grip handle with internal bits storage. 12 chrome plated alloy steel 1/4" sockets on 2 removable plastic clips. 32 high grade bits with rust resistant finish also on removable plastic clips. Contents - 3, 4, 4.5, 5, 6, 7, 8, 9mm Slotted. PH 0, 1, 2, 3. PZ 0, 1, 2, 3. Hex 1.5, 2, 2.5, 3, 4, 5, 5.5, 6mm. Tamperproof T 08, T 10, T 15, T 20, T 25, T 27, T 30, T 40. 1/4" square drive METRIC sockets 6, 7, 8, 10, 11, 13mm. 1/4" square drive A/F sockets 3/16, 1/4, 5/16, 11/32, 3/8 and 7/16". 1/4" square drive adaptor and spare socket and bits.



4829 Ratchet screwdriver

Item Number	i
T4829D	ratchet screwdriver

With magnetised shaft to hold blades, high torque ratchet with left, right hand and neutral action. Supplied with 10 bits. Bits held in magazine in cushioned plastic fluted handle. Display packed. Contents Bits held in handle - 3mm, 4.7mm and 6.3mm. Slotted 6.3mm. Hex 3, 4, 5mm. PZ 1, 2. PH2.