

SAUTER CK 600-0P1

Miniature load cell made of aluminium

KERN



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CK P1

Measuring System

Weighing capacity [Max]	600 g
Load cell - characteristic value - nominal	1 mV/V
Load cell - characteristic value - variance	0,15 mV/V
Load cell OIML class	C2
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Directions of force	compression
Load cell - Input resistance - nominal	1055 Ω
Load cell - Output resistance - nominal	1000 Ω
Load cell - Input resistance - variance	10 Ω
Load cell - Output resistance - variance	10 Ω
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	9 V
Load cell - Isolation resistance - [Min]	2000 M Ω
Load cell - Combined error	0,03%
Temperature coefficient - characteristic value	$\pm 0.03\%$ F.S. / 10 °C

Zero balance	$\pm 0,1\text{mV/V}$
Temperature coefficient - zero signal	$\pm 1\%$ F.S. / 10 °C
Creep error (30 minutes)	$\pm 0.03\%$ FS/5min
Safe overload	150%
Ultimate overload	300%

Functions

IP protection - complete device	IP65
---------------------------------	------

Construction

Material	aluminium
Design	Miniature bending beam
Dimension (W×D×H)	80×10×12,7 mm
Cable length	0,25 m
Mounting - force application	2 × threaded hole M4
Mounting - force dissipation	2 × threaded hole M5

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	65 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkKS calibration (compressive force)	963-261V
--	----------

Product information

GTIN/EAN number	4045761221086
Trade number	84239010
REACH classification	no prohibited substances

Packing & Shipping

Shipping method	Parcel service
Delivery time	1 d
Dimensions packaging (W×D×H)	145×60×35 mm
Net weight approx.	0,05 kg
Gross weight approx.	0,10 kg
Shipping volume weight	0,1 kg

SAUTER CK 600-0P1

Miniature load cell made of aluminium

KERN

Pictograms

STANDARD



OPTION

