

SINGLE USE GLOVE, 100% NITRILE, POWDER FREE, SILICONE FREE, 300MM LONG, 0.20MM THICK

Single-use nitrile glove with high performance against penetration and projection of chemicals. Low modulus formulation to improve fit and reduce fatigue.

FEATURES

- › Single-use 100% nitrile disposable glove
- › Powder-free and approved for food-handling
- › Second skin feel, softer texture and easy donning
- › Latex-free to avoid type I and type IV latex allergies
- › Chlorinated to offer more comfort, grip and reduce tackiness
- › Textured finish on fingertips to enhance grip
- › Low-modulus formulation to improve fit and reduce fatigue
- › Dual labelling: PPE and medical
- › Category III, EN374 and EN455 approved
- › Antistatic properties due to inherent antistatic properties of nitrile
- › Resistant against viruses according to ASTM F 1671:2007
- › Force at break: 20N
- › Length: 300mm
- › Thickness: 0.20mm
- › AQL 0.65



Textured finish on fingertips

SUITABLE FOR


Typical Industries

- Aerospace
- Electronics
- Food
- Laboratory
- Medical
- Pharmaceutical
- Printing

Suitable Applications

- Chemical Handling
- Emergency Services
- Food Handling
- Glass
- Handling Oily Components
- Light Assembly

CERTIFICATION



See overleaf for explanation

PRODUCT INFORMATION

MATERIALS	LINER:	Nitrile
COLOUR	Cobalt Blue	
LENGTH (mm)	300	
CUFF STYLE	Beaded	

ORDERING DETAILS

SIZE	CODE	PACKAGING
S	SHO75851	50 singles per box
M	SHO75852	20 boxes per case
L	SHO75853	
XL	SHO75854	

RECOMMENDATIONS FOR USE

- Do not use in cases of heavy chemical exposure, electrical or thermal risk.
- Store away from light and humidity.

CERTIFICATION LEGENDS



SPECIFIC CHEMICAL PROTECTION
EN 374

LETTER CHEMICAL
CODE PRODUCT

A	Methanol	G	Diethylamine
B	Acetone	H	Tetrahydrofuran
C	Acetonitrile	I	Ethyl acetate
D	Dichloromethane	J	n-Heptane
E	Carbon Disulfide	K	Sodium hydroxide 40%
F	Toluene	L	Sulphuric acid 96%



FOOD CONTACT
DIRECTIVE 2002 / 72 EC




MICRO-ORGANISMS



MECHANICAL
HAZARDS
EN 388: 2003

PERFORMANCE LEVELS



ABOUT GLOBUS

World leader in protecting hands, Globus serves organisations with bespoke hand protection solutions built from a professional range of high performance protective gloves.

Globus is proud to offer bespoke solutions that deliver robust commercial benefits not just safety improvements. We have an enviable track record in helping to reduce hand accident rates whilst delivering improved comfort and productivity as well as waste and cost reductions.

Globus applies its expertise across a spectrum of industries, meeting and exceeding a diverse range of hand protection requirements; from the rigorous demands of the petrochemical and construction industries to the complexities of clean room and aerospace manufacturing.

Find out why leading companies rely on a solution from Globus to help implement a comprehensive hand protection policy. Contact us today.

UK AND IRELAND

www.globus.co.uk

E: sales@globus.co.uk

T: +44 (0)161 877 4747

F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com

T: +971 4 882 9962

F: +971 4 882 9963

