

CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/gb/products/3240284>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universal wire holding bracket, perforated, for wiring channels

Commercial data

Item number	3240284
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	BE743Z
Product key	BE743Z
Catalog page	Page 581 (C-3-2019)
GTIN	4046356478472
Weight per piece (including packing)	3.8 g
Weight per piece (excluding packing)	5.72 g
Customs tariff number	39269097
Country of origin	DE

CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/gb/products/3240284>

Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Dimensions

Width	76.5 mm
Height	20.1 mm
Depth	21.4 mm
Length	20.1 mm

Material specifications

Color	stone gray (RAL 7030)
Material	PS-HF
Components	Lead-free

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

CD WR - Universal wire retaining clip

3240284

<https://www.phoenixcontact.com/gb/products/3240284>



Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240284>



VDE approval of drawings

Approval ID: 40058456

DNV

Approval ID: TAE00004VN

CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/gb/products/3240284>

Classifications

ECLASS

ECLASS-13.0	27400765
-------------	----------

ETIM

ETIM 9.0	EC001018
----------	----------

UNSPSC

UNSPSC 21.0	31163000
-------------	----------

CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/gb/products/3240284>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk