



ALPHA 400, wall-mounted cabinet, IP44, Protection class 2, H: 800 mm, W: 300 mm, T: 210 mm, RAL 9016

| Model                                              |     |                      |       |
|----------------------------------------------------|-----|----------------------|-------|
| product brand name                                 |     | ALPHA                |       |
| product designation                                |     | Wall-mounted cabinet |       |
| design of the product                              |     | Surface mounting     |       |
| surface processing                                 |     | powder-coated        |       |
| Protection class                                   |     |                      |       |
| protection class IP                                |     | IP44                 |       |
| operating resource protection class                |     | Safety class 2       |       |
| IK protection class                                |     | IK09                 |       |
| suitability for interaction lightning protection   |     | Yes                  |       |
| suitability for use for outside use                |     | No                   |       |
| Appearance                                         |     |                      |       |
| RAL color number                                   |     | 9016                 |       |
| product component                                  |     |                      |       |
| • cable entry                                      | Yes |                      |       |
| • mounting plate                                   | No  |                      |       |
| product extension optional side-by-side mounting   |     | Yes                  |       |
| number of rows                                     |     | 5                    |       |
| Mechanical Design                                  |     |                      |       |
| height                                             |     | 800 mm               |       |
| width                                              |     | 300 mm               |       |
| depth                                              |     | 210 mm               |       |
| installation depth                                 |     | 210 mm               |       |
| number of modular width units                      |     | 60                   |       |
| number of modular width units per DIN mounting bar |     | 12                   |       |
| fastening method                                   |     | surface mounting     |       |
| net weight                                         |     | 10 kg                |       |
| material of the enclosure                          |     | Steel                |       |
| Approvals Certificates                             |     |                      |       |
| General Product Approval                           |     | Test Certificates    | other |




[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

Environment

[Environmental Con-](#) [Environmental Con-](#)

**Further information****Information on the packaging**<https://support.industry.siemens.com/cs/ww/en/view/109813875>**Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1132-3KA12>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/8GK1132-3KA12>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1132-3KA12](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1132-3KA12)**CAX-Online-Generator**<http://www.siemens.com/cax>**Tender specifications**<http://www.siemens.com/specifications>

last modified:

5/26/2025 

