

Comfortable nitrile work gloves, delivering advanced mechanical and chemical protection

- **Advanced protection:** AlphaTec® 58-330 hand protection gloves are coated with a superior nitrile film for excellent protection against chemicals, snags, punctures and abrasion
- **Elevated comfort:** These protective gloves feature AQUADRI™ Moisture Management Technology, which offers a highly absorbent inner soft foam coating that reduces sweat buildup significantly, providing greater comfort and performance
- **Enhanced grip:** The AlphaTec® 58-330 abrasion-resistant gloves' reverse lozenge palm finish ensures a secure wet and dry grip
- **Added feature:** The foldable cuff gutter on these green chemical gloves prevents dripping on the forearm
- **Food handling compliance:** As these food safety gloves comply with the FDA food handling requirements, they are suitable for food applications



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Assembly & inspection of components
- Oil, fluids and filter change
- Painting or cleaning tools or robots
- Plating, coating, sealing, painting
- Handling incoming goods
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process

Key Features

- **High-performance nitrile compound:** Superior mechanical protection
- **AQUADRI™ Technology:** Cooler and dryer safety gloves for extended wear
- **Reverse lozenge palm finish:** Improved wet and dry grip

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate (ZDEC)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



AQUADRI™

Moisture Management Technology



Performance Standards

EN 388: 2016



3101X

EN ISO 374-1:2016



JKLOPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-330	Liner Material: Aquadri® 2 Coating Material: Nitrile Featured Technology: AQUADRI™	7, 8, 9, 10, 11	320 / 12.6	Green	• 12 pairs/polybag; 12 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.