



CIRCULAR ORBITAL HSS BLADES

ERKO OBK-X: ORBITAL CIRCULAR BLADES STEEL AND STAINLESS STEEL




Technology: high-speed steel HSS-CoV with 5% cobalt.

Application: cutting steel and stainless steel tubes.

Benefits:

- perfect straight cut
- burr-free and clean cut
- fast cutting
- repeatability and productivity



References	Designation	min recom thickness	max recom thickness	Packaging	EAN13
OBX63-16-16-T45	ORBITAL HSS-CoV SAW BLADE OBK-X 63x1.6x16 T4.5 Z44	2 mm	7 mm	10	3700333211674
OBX63-16-16-T3	ORBITAL HSS-CoV SAW BLADE OBK-X 63x1.6x16 T3 Z64	1 mm	3 mm	10	3700333211698
OBX68-16-16-T45	ORBITAL HSS-CoV SAW BLADE OBK-X 68x1.6x16 T4.5 Z44	2 mm	7 mm	10	3700333211971
OBX68-16-16-T3	ORBITAL HSS-CoV SAW BLADE OBK-X 68x1.6x16 T3 Z72	1 mm	3 mm	10	3700333211681
OBX68-16-16-T25	ORBITAL HSS-CoV SAW BLADE OBK-X 68x1.6x16 T2.5 Z84	0,7 mm	2,5 mm	10	3700333211704
OBX80-20-16-T45	ORBITAL HSS-CoV SAW BLADE OBK-X 80x2.0x16 T4.5 Z54	2 mm	7 mm	10	3700333211988
OBX80-20-16-T3	ORBITAL HSS-CoV SAW BLADE OBK-X 80x2.0x16 T3 Z80	1 mm	3 mm	10	3700333211711

Other dimensions available upon request



Photo credit: System Weld
Welding Training / www.systemweld.com

ERKO OBK-X-ALTIMINIUM :

COATED BLADE FOR
HIGH-VOLUME PRODUCTION:
INCONEL, DUPLEX, AND SUPERDUPLEX STEELS

Technology: High-speed steel HSS-CoV with 5% cobalt, ALTIMINIUM coating.

Application: Serial cutting of Inconel, duplex, and superduplex steel tubes.

Benefits:

- perfect straight cut
- burr-free and clean cut
- fast cutting
- repeatability and productivity
- very high productivity (ALTIMINIUM coating)
- extreme durability (ALTIMINIUM coating)



References	Designation	Thick min-max	Pack	EAN13
OBX-ALT63-16-16-T45	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 63x1,6x16 T4,5 Z44	2 - 7 mm	10	3700333211902
OBX-ALT63-16-16-T3	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 63x1,6x16 T3 Z64	1 - 3 mm	10	3700333211919
OBX-ALT68-16-16-T45	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 68x1,6x16 T4,5 Z44	2 - 7 mm	10	3700333211926
OBX-ALT68-16-16-T3	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 68x1,6x16 T3 Z72	1 - 3 mm	10	3700333211933
OBX-ALT68-16-16-T25	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 68x1,6x16 T2,5 Z84	0,7 - 2,5 mm	10	3700333211940
OBX-ALT80-20-16-T45	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 80x2,0x16 T4,5 Z54	2 - 7 mm	10	3700333211957
OBX-ALT80-20-16-T3	ORBITAL BLADE HSS-Co OBK-X ALTIMINIUM 80x2,0x16 T3 Z80	1 - 3 mm	10	3700333211964