


Separation main busbar, mounting position: top, W: 1000 mm D: 400 mm



| Model                                       |                               |
|---------------------------------------------|-------------------------------|
| product brand name                          | SIVACON S4                    |
| product designation                         | separation main busbar system |
| design of the surface                       | other                         |
| General technical data                      |                               |
| design                                      | assembly kit                  |
| suitability for use                         | for main busbar at top        |
| RAL color number                            | other                         |
| color                                       | miscellaneous                 |
| Product details                             |                               |
| product component                           |                               |
| • cable entry                               | No                            |
| • lock                                      | No                            |
| Mechanical Design                           |                               |
| height                                      | 225 mm                        |
| width                                       | 1 000 mm                      |
| depth                                       | 400 mm                        |
| installation width for cabinet installation | 1 000 mm                      |
| installation depth for cabinet installation | 400 mm                        |
| shape of inner subdivisions                 |                               |
| • shape 2a                                  | Yes                           |
| • shape 2b                                  | Yes                           |
| • shape 3a                                  | No                            |
| • shape 3b                                  | No                            |
| • shape 4a                                  | No                            |
| • shape 4b                                  | No                            |
| mounting position                           | top                           |
| net weight                                  | 9.6 kg                        |
| material                                    | sheet-steel                   |
| Certificates                                |                               |
| reference code according to IEC 81346-2     | UC                            |
| Approvals Certificates                      |                               |
| General Product Approval                    | other                         |



[Miscellaneous](#)



[Confirmation](#)

Environment

#### Further information

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ3000-1BA13>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ3000-1BA13>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ3000-1BA13](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ3000-1BA13)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

---

last modified:

7/19/2022 

