



# Componex Vu Mini-Meters - stock range

## Rectangular Vu Indicators



- Flush mounting
- Professional appearance
- Low cost solution
- Easy to back light
- Minimum depth
- Robust
- Ex-stock availability


The meters are robust, low-cost, back-of-panel rectangular Vu moving coil indicators with red and black scaling on a buff background. They can be illuminated by placing a bulb behind the translucent scale.



Order Code	Sensitivity ±20%	Resistance ±15%	0 Vu	Internal illumination	Rec. Price £:					
					1+	5+	10+	25+	50+	100+
SU6	0-200 $\mu$ A	650 $\Omega$	130 $\mu$ A	no						
ST7	0-200 $\mu$ A	650 $\Omega$	130 $\mu$ A	no						
SQ10	0-500 $\mu$ A	600 $\Omega$	270 $\mu$ A	8V 50mA						
SM14	0-500 $\mu$ A	600 $\Omega$	270 $\mu$ A	8V 50mA						


Dimensions mm	A	B	W	D	H	I
SU6	40.00	40.00	21.5 x 36.5 x 3.0	20.00	8.00	12.50
ST7	55.00	47.50	50.0 x 28.0 x 3.0	18.50	7.00	14.00
SQ10	64.50	53.50	60.0 x 35.0 x 3.0	18.00	12.00	13.00
SM14	79.20	63.00	73.7 x 37.6 x 3.0	26.50	12.00	13.00

## Circular Vu Indicators



- Circular window
- Professional appearance
- Low cost solution
- Easy to back light
- Minimum depth
- Retro-fit look
- Ex-stock availability

These "retro-style" meters are robust, low-cost, back-of-panel circular Vu moving coil indicators. They can be illuminated by placing a bulb behind the translucent scale. The meters are mounted through a single circular hole.



Order Code	Sensitivity ±20%	Resistance ±15%	0 Vu	Internal illumination	Rec. Price £:					
					1+	5+	10+	25+	50+	100+
C220VU	0-200 $\mu$ A	650 $\Omega$	130 $\mu$ A	no						
C360VU	0-200 $\mu$ A	650 $\Omega$	130 $\mu$ A	no						
C450VU	0-200 $\mu$ A	650 $\Omega$	130 $\mu$ A	no						

Dimensions mm	mm						
	A	B	C	D	F	H	I
C220VU	26.00	32.00	22.00	18.00	1.50	8.00	14.00
C360VU	40.00	40.00	35.80	20.00	5.00	8.00	12.50
C450VU	55.00	47.50	44.80	18.50	5.00	8.00	14.00

AVAILABLE FROM: NATIONAL DISTRIBUTORS OR DIRECT FROM ANDERS IN MULTIPLES OF 10 PCS AND SUBJECT TO A MOQ OF 50 PCS.

CMMP5B/Revision 5 03/06/04

PAGE 5

**anders electronics plc** Bayham Place, London NW1 0EU UK  
Tel: +44 (0)20 7380 8167 Fax: +44 (0)20 7874 1908 <http://www.anders.co.uk>

Anders Electronics plc (Anders) does not warrant the accuracy or completeness of the information contained herein, the supply of products by Anders is subject to its standard terms and conditions of sale. Prior to concluding any agreement with Anders the customer should satisfy itself of the accuracy and completeness of the information contained herein and should notify to Anders any intended use of the product.  
[www.anders.co.uk](http://www.anders.co.uk) | [info@anders.co.uk](mailto:info@anders.co.uk)

