

# KWX RANGE

## KWX205 Rigger Safety Boot – S3/S2



**KING'S**

by Honeywell

*The Logical Choice*



**Description:** Water Resistant Leather Pull-Up Safety Boot

**Size:** UK 3-13 | US 4-14 | EU 36-48

**Application:** Infrastructure, Mining, Heavy Industries, Oil and Gas

**Standard:** SR [EN ISO 20345:2022]; S3/S2



SKU	Steel Midsole	Color	Outsole	Category
KWX205	Yes	Black	Dual Density PU	S3
KWX205X	No	Black	Dual Density PU	S2
KWX205C	Yes	Brown	Dual Density PU	S3
KWX205CX	No	Brown	Dual Density PU	S2

### Features:

- Water resistant and tough 2.0 - 2.2 mm thick full-grain leather upper with good breathability.
- Side pull-up straps for easy donning and doffing even when wearing gloves.
- Innovative outsole cleaning system with unique groove design helps expel dirt and mud that gather within the sole channels, ensuring your footwear maintains its optimal grip and performance even in challenging environments.
- Grip Zone on outsole offers enhanced grip and slip resistance on rugged terrains.
- Deeper, more aggressive grooves for greater grip on slippery surfaces and prolonged slip resistance.
- Enhanced outsole thickness to deliver exceptional cushioning and comfort with every step.
- Driver-centric stabiliser on outsole enhances foot positioning

for vehicle drivers to ensure an optimised stance for heightened comfort and unparalleled control.

- Strong leather upper and sole bond to withstand demanding work environments.
- King's signature wide profile steel toecap for greater comfort.
- King's Comfort Footbed features ultra-breathable perforated channels for quick drying and all-day feet freshness.
- Highly breathable 3-D lining minimises skin abrasion, keeps feet insulated and effectively wicks away moisture.
- Lightweight, shock absorbing dual density polyurethane (PU) sole for added comfort.
- Excellent slip resistant sole delivers durable traction; SR [EN ISO 20345:2022]; Anti-static.
- Sole resistant to mineral and organic oils.

### SOLE FEATURES



Puncture Resistant



Anti-Static



Slip Resistant



Self-Cleaning Sole



Mineral Oils Resistant



Organic Oils & Fats Resistant

### COMFORT FEATURES



Wide Profile Toecap



Breathable Lining



Comfort Footbed



Impact Absorption



Lightweight

### FOOTWEAR FEATURES



Water Resistant Leather



2.0 - 2.2 mm Full Grain Leather



Driver Centric Stabiliser



Toe Bumper



Steel Safety Toecap



LEARN MORE  
automation.honeywell.com

KWX205 | v1.1 / 24  
© 2024 Honeywell International Inc.