

Previously known as: MICROGARD® 2300 PLUS - Model 132

Lightweight, antistatic protective suit, offering a medium-duty barrier against various inorganic chemicals.

- **Specialized protection:** With a polyethylene barrier and bi-component nonwoven inner layer, the AlphaTec® 2300 PLUS Stitched & Taped - Model 132 chemical-protective suit guards against various inorganic chemicals* (including acids and bases), while remaining durable, lightweight and flexible
- **Increased visibility:** Its yellow color ensures it remains highly visible, for noticeable personal protection and improved workplace safety
- **Enhanced features:** This AlphaTec® protective suit also includes a thumb loop, respirator fit hood and secure zip flap with self-adhesive tape closure, as well as over-taped inner stitching, for added strength
- **Certified antistatic capabilities:** It is tested in accordance with EN 1149-5 antistatic standards

*CE Category III Type 3/4/5 protection



Industries

- Life Sciences
- Machinery and Equipment
- Agriculture
- Food Processing


Applications

- Transferring liquids and solids between vessels and tanks and process equipment
- Unexpected leakages spills or other releases
- Loading and unloading of trucks and vehicles
- Filling, blending and charging of raw materials
- Product inspection
- Mixing or loading chemicals
- Cleaning of plant and machines


KEY FEATURES & BENEFITS

- **Protective barrier:** Inorganic liquid chemical (acids, bases) resistance
- **Polyethylene, dual-layer design:** For lightweight safety and durability
- **Bright yellow color:** High visibility, for enhanced workplace safety

Material Diagram



Seam Diagram



Performance Standards



Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL, 4XL, 5XL
Color	Yellow
Country Of Origin	China, Sri Lanka
Packaging Overview	Individually packaged
Product Material	Polyethylene on bicomponent Polypropylene/Polyethylene non-woven
Product Reference	2300 PLUS - Model 132
Seam Type	Stitched and Taped
Shelf Life	5 years
Style Number	Y23T132

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall, 3-piece hood, 2 way front zipper with re-sealable storm flap, finger loops. Elasticated hood, waist, wrists and ankles.

For additional in formation visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

