



## REVERSIBLE REVOLVER DRILL WITH AUTO CHUCK 13MM

**RC214A**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:27





## DESCRIPTION

### REVERSIBLE REVOLVER DRILL WITH AUTO CHUCK 13MM

**POWERFUL** Its high torque level (550 W - 800 rpm) allows you to carry out heavy-duty drilling jobs in industrial maintenance. **COMFORTABLE** Its handle with a flared base, tilted at 4° and its imprints for your fingers ensures an excellent grip and therefore a good position when pushing on difficult materials. **Reversible drill.** Aluminium casing. **Progressive trigger.** **Rear exhaust.** **Comfortable handle** insulating against the cold. **Directable auxiliary handle.** Can be fitted with a noise reduction pipe.

## STANDARDS / DIRECTIVES

2006/42/CE, ISO 15744

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:27



**SPECIFIC DATA**

Designation	REVERSIBLE REVOLVER DRILL WITH AUTO CHUCK 13MM
Sales reference	RC214A
L (mm)	205
Weight (g)	1910
l (mm)	45
h (mm)	155
Power (W)	550
C min mm	13
Rotation speed (rpm)	800
Vibration (m/s <sup>2</sup> )	2,5
Noise level (dBa)	89
C mm	6,5
C min mm	200
C mm	1/4
Guarantee	M2   SAM Equipment and Machine Guarantee

**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

