

PRODUCT-DETAILS

TY175-50-100

CBL TIE 7IN NATURAL NYL 50LB



General Information

Extended Product Type	TY175-50-100
Product ID	7TAG054360R0157
EAN	5414363075158
Catalog Description	CBL TIE 7IN NATURAL NYL 50LB
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius for Indoor Applications, UL/IEC 62275 Type 2/21 Rated for AH-2 Plenum, Length of 188mm, Width of 4.7mm, Thickness of 1.2mm, Tensile Strength Rating of 220 Newtons, 100 Pack

Ordering

EAN	5414363075158
UPC	786210918068
Country of Origin	Hungary (HU) United States (US)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.184 in 4.674 mm
Product Net Depth / Length	188 mm 7.402 in

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	13.1 in 333 mm
Package Level 1 Height	9.1 in 231 mm
Package Level 1 Depth / Length	20.7 in 526 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	9.25 in 235 mm
Package Level 2 Height	4.75 in 121 mm
Package Level 2 Depth / Length	9.5 in 241 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	44 mm 1.732 in
Color	Natural
Effective Date	19930630
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	PLASTIC CABLE TIE
Product Type	General Purpose
Special Functions	"The integrally formed polyamide pawl combines low insertion and high locking strength. The low profile head significantly reduces the potential for snagging during installation. Quick and easy pull through increases productivity, reduces operator fatigue. Tail with finger grip design that helps operator grasp and pull ties snugly. Sure grip tab keeps the tail from popping out while being treated, then holds it it securely for final tightening by hand or tool"
Standards	UL E49405
Tensile Strength	222 N 50 lb
Thickness	1.2 mm 0.047 in

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000751
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY175-50-100
REACH Declaration	9AKK108466A3876
RoHS Information	9AKK108466A3872

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

