

Features

- Aluminium padlock
- Plastic-coated
- Available in various colours
- Keyed Alike
- Key lock type
- Keys
- For indoor and outdoor use

RS PRO Key Padlock, Keyed Alike – 43 mm

RS Stock No: 195-8228, 195-8229, 195-8230,
195-8231, 195-8232, 195-8233



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Keyed Alike Padlock, 43 mm

Keep sensitive equipment and restricted-access gates secure with this RS PRO padlock. It comes with two keys to grant you and one other person access, or to give you a spare. Push the shackle down to initiate the automatic locking for quick protection. Lock-picking is deterred by the paracentric keyway that creates an intricate lock path.

The mechanism and shackle are coated in an aluminium layer to keep them resistant to corrosion, so the lock won't rust up over time, even when in contact with chemicals. The colour cover makes the lock easily noticeable, alerting people of the restricted access. The mechanism is coated in a strong plastic to conceal it and provide an extra layer of protection from would-be lock-breakers.

General Specifications

Material	Aluminium, Steel
Out Cover	Plastic Coated
Shackle Dia.	6 mm
Shackle Length	22 mm
Body Width	43 mm
Colour	Various Colours Available Separately

Similar Products

RS Stock no	Product Name	Colour
195-8228	RS PRO Key Aluminium, Steel Padlock, Keyed Alike, 6mm Shackle, 43mm	White
195-8229	RS PRO Key Aluminium, Steel Padlock, Keyed Alike, 6mm Shackle, 43mm	Black
195-8230	RS PRO Key Aluminium, Steel Padlock, Keyed Alike, 6mm Shackle, 43mm	Red
195-8231	RS PRO Key Aluminium, Steel Padlock, Keyed Alike, 6mm Shackle, 43mm	Violet
195-8232	RS PRO Key Aluminium, Steel Padlock, Keyed Alike, 6mm Shackle, 43mm	Yellow
195-8233	RS PRO Key Aluminium, Steel Padlock, Keyed Alike, 6mm Shackle, 43mm	Blue

RS Article No.	Lock Body Dimesion(mm)			Shackle Dimesion(mm)			Color	Keyed Alike
	A	B	C	D	E	F		
1958228	43	33	17	6	21	22	White	KA8
1958229	43	33	17	6	21	22	Black	KA9
1958230	43	33	17	6	21	22	Red	KA10
1958231	43	33	17	6	21	22	Violet	KA11
1958232	43	33	17	6	21	22	Yellow	KA12
1958233	43	33	17	6	21	22	Blue	KA13