

FloorPro Wipe Care Extra RM 780

Polymer-based wipe care without layer build-up for maintenance cleaning of all water-resistant hard and resilient flooring. Anti-slip properties in accordance with DIN V 18032-2:2001-04.

pH value 9
in concentrate



NTA-free



Properties

- Everyday cleaner for all water-resistant hard and elastic floors
- Removes oil, grease and mineral contamination
- Particularly suitable for use in sports halls and multi-purpose halls
- Suitable for sports halls and multi-purpose halls, anti-slip in accordance with DIN V 18032-2:2001-04 (depending on the floor covering)
- Also suitable for cleaning all types of resilient floor coverings for the first time
- Contains care components (water-soluble polymers)
- Suitable for polishing
- Gentle on materials
- Low-foam formulation
- Pleasant, fresh scent
- Solvent-free
- Ideal complement to RM 784 Care Dispersion and RM 782 Protect Dispersion

Usage options

- Scrubber driers
- Manual

Application areas

Car dealership and garage	Floor cleaning
Building cleaning	Floor cleaning
Nursing and retirement homes, doctor's surgeries	Floor cleaning
Hotels, gastronomy, catering	Floor cleaning
Industry	Floor cleaning
Municipal	Floor cleaning
Retail	Floor cleaning

Technical data

Container sizes	Packaging unit	Part number
2.5 l	4 Piece(s)	6.295-580.0
10 l	1 Piece(s)	6.294-997.0
20 l	1 Piece(s)	6.295-468.0

Application

Scrubber driers – maintenance cleaning

- Remove coarse dirt by sweeping.
- Use appropriate brush/roller/pad and squeegee for scrubber drier as required.
- Combine the product with the appropriate dosage and fresh water.
- On DOSE machines, set the dosing only on the device.
- Clean and vacuum the surface with a scrubber dryer using the 1-step method.
- Polish with one disc machine where necessary.

Manual

- Remove coarse dirt by sweeping.
- Combine the product with the appropriate dosage and fresh water.
- Clean surface manually.
- Polish with one disc machine where necessary.

Instructions for use

- Do not apply to wood or unsealed parquet flooring.
- Keep container closed tightly.
- Store away from frost.

Warnings and safety recommendations according to EC Directives

- EUH 210 Safety data sheet available on request.

Further information

- Expert report on slip resistance in accordance with DIN V 18032-2:2001-04
- Material Safety Data Sheet (MSDS)

Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1000 ml	Scrubber driers – maintenance cleaning	0.25 – 3 %	mild-medium	4890 m²
1000 ml	Manual – maintenance cleaning	0.25 – 3 %	mild	6000 m²