



## MATERIAL FACT SHEET

### 332847 R00CPU

#### General Data

Product Hierarchy	IAD51401
	Modular PLC
	IQ-R Standard
Ext. Material Group	10 STANDARD ITEM
ABC Indicator	B (Limited Availability from Stock)

e-shop: <https://emea.mitsubishielectric.com/fa/shop/material-page/000000000000717286>

#### FA-MOD PLC: CPU Module

Series	MELSEC IQ-R SERIES
Type	STANDARD CPU
Program Memory	10K
Program Memory Unit	STEPS
Local I/O Points	4096
Local + Remote I/O Points	4096
Cycle Time LD (ns)	31,3
Cycle Time MOV (ns)	62,7
USB	1
Ethernet Port	1
Buffer Battery	YES
Int. Current Consumption (A)	0,67

#### Product Dimensions & Weight

Width (mm)	27,8
Height (mm)	106
Depth (mm)	110
Weight (kg)	0,2

#### Logistic Dimensions & Gross Weight

Length (cm)	14,5
Width (cm)	16,0
Height (cm)	5,0
Gross Weight (kg)	0,220
Volume (cdm)	1,160

#### Stock Data

Planned Delivery Time (Days)	94
------------------------------	----

#### Life Cycle

Sales Start	01.02.2018
Predecessor	138323 / Q00CPU

#### Additional Product Information

Binding Tariff Information	DEBTI-52748/20-1
BTI validity date	27.06.2024
Battery included	NO

#### Export Data

Commodity Code	85371091
Legal Control (Dual Use List)	Not Listed
Country of Origin	Japan (JP)
Preference Status (Supplier Declaration)	Non EU

#### Environmental

REACH Limit Exceeded	YES
----------------------	-----

REACH Substance CAS Number	<a href="#">1303-86-2</a>
REACH Substance CAS Number (2)	<a href="#">71868-10-5</a>
REACH Substance CAS Number (3)	<a href="#">7439-92-1</a>
REACH Substance CAS Number (4)	<a href="#">80-43-3</a>
Dangerous Goods Class	NO
Dangerous Goods Identifier	NO
RoHS Compliance	COMPLIANT
WEEE	B2B

### Conformity

CE	COMPLIANT
UL/cUL	COMPLIANT
EAC	NON-COMPLIANT
UKCA	COMPLIANT

### Documentation & Media Data

Manual URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=bltdae25c2bd5f2ff94&amp;q=R00CPU&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=bltdae25c2bd5f2ff94&amp;q=R00CPU&amp;doc-lang=en</a>
Certificates URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt8050dd1408c11cc2&amp;q=R00CPU&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt8050dd1408c11cc2&amp;q=R00CPU&amp;doc-lang=en</a>
CAD URL Indicator	<a href="https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt26ecc97a31a841c1&amp;q=R00CPU&amp;doc-lang=en">https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&amp;doc-cats=blt26ecc97a31a841c1&amp;q=R00CPU&amp;doc-lang=en</a>

### Product Packaging

Cardboard (g)	45
Other paper (g)	26
Aluminum (g)	0
Steel (g)	0
Styrofoam (g)	0
Other plastic (g)	3
Wood (g)	0
Glass (g)	0
Others (g)	0

### Compatible products

Material	Description / Price List Text / Classification
<a href="#">165286</a>	FX3U-32BL Battery Battery for PLC types FX3 / FX5 Class 100100112: FA-COM PLC: Spare Part
<a href="#">165286</a>	FX3U-32BL Battery Battery for PLC types FX3 / FX5 Class 100101303: FA-OTHERS: Battery
<a href="#">221540</a>	USB-CAB-5M USB 2.0 connection cabel, plug USB A to plug USB B (mini), 5m Class 100100303: FA-HMI: Cable
<a href="#">284378</a>	GX Works3 2L-USB PLC Programming Software for MELSEC iQ-R/F, English, 2 Licences USB Class 100101201: FA-Software: Software PLC
<a href="#">284379</a>	GX Works3 5L-USB PLC Programming Software for MELSEC iQ-R/F, English, 5 Licences USB Class 100101201: FA-Software: Software PLC
<a href="#">286227</a>	iQ Works 2L-USB iQ Works V2.0,inc Navigator/GX/GT/MT Works/RT Toolbox3 inc SIM,Eng,2 Licence USB Class 100101201: FA-Software: Software PLC
<a href="#">286228</a>	iQ Works 5L-USB iQ Works V2.0,inc Navigator/GX/GT/MT Works/RT Toolbox3 inc SIM,Eng,5 Licence USB Class 100101201: FA-Software: Software PLC
303426	iQ Works V02-15L0C-E iQ Works V2.0,incl Navigator,GX Works,GT Works,MT Works;engl;USB;15 PC's Class 100101201: FA-Software: Software PLC
304614	GX Works3 V01-2L0C-G PLC Programming SW; Melsec iQ-R/iQ- F only (no GXW2/GX Dev); USB; 2 PCs; German Class 100101201: FA-Software: Software PLC
304645	GX Works3 V01-5L0C-G PLC Programming SW; Melsec iQ-R/iQ- F only (no GXW2/GX Dev); USB; 5 PCs; German Class 100101201: FA-Software: Software PLC
308856	GX Works3 V01-2L0C-IT PLC Programming-S/W for Melsec iQ-R/iQ- F;engl;USB;2 PC's; Italian Class 100101201: FA-Software: Software PLC

Material	Description / Price List Text / Classification
338821	iQ Works V02-2L0C-G iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;German;USB;2 PC´s Class 100101201: FA-Software: Software PLC
339022	iQ Works V02-5L0C-G iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;German;USB;5 PC´s Class 100101201: FA-Software: Software PLC
401853	iQ Works V02-2L0C-IT iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;Italian;USB;2 PCs Class 100101201: FA-Software: Software PLC
<a href="#">697551</a>	IE-C6A-0.2m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.2m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697582</a>	IE-C6A-0.5m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.5m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697583</a>	IE-C6A-1.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 1.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697584</a>	IE-C6A-2.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 2.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697585</a>	IE-C6A-5.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 5.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697586</a>	IE-C6A-10.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 10.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697587</a>	IE-C6A-15.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 15.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697588</a>	IE-C6A-20.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 20.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697589</a>	IE-C6A-25.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 25.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
<a href="#">697590</a>	IE-CB-1piece CC-Link Bending tool for Patch Cable, RJ45, 1 piece, 90°Deg radius Class 100100215: FA-MOD PLC: Other Option
<a href="#">697591</a>	IE-C6A-CON-1pc CC-Link IE Certified Patch Cable connector, easy clip, RJ45, Cat.6A, 1pc Class 100100215: FA-MOD PLC: Other Option
<a href="#">717285</a>	EDS-G2008-EL 8Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module
<a href="#">717286</a>	EDS-G2005-EL 5Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module