



 PRODUCT-DETAILS

CL2-520R

CL2-520R Pilot Light



360°

概要信息

产品型号	CL2-520R
产品ID	1SFA619403R5201
欧洲商品编号(EAN)	7320500556337
目录说明	CL2-520R Pilot Light

详细描述	<p>The CL2-520R Pilot Light is: Compact - Pilot Light - Pilot light head - Red - Illuminated - 220V DC</p> <p>This Pilot Light is part of ABB's compact range, the most efficient all-in-one solution available, reducing installation time and cost.</p> <p>The compact range has a high level of dust and water resistance.</p>
------	---

订货信息

最小起订量	10 piece
海关关税号	8536619090

Popular Downloads

数据手册, 技术资料	1SFC151007C02_
------------	----------------

尺寸

产品净宽	0.03 m
产品净高	0.03 m
产品净深	0.052 m
产品净重	0.018 kg

技术参数

周围环境温度	Operation -25 ... +70 °C Storage -40 ... +85 °C
颜色	Red
驱动器类型	Pilot light head
照明	Illuminated
灯类型	220 V DC, integrated LED
外壳防护等级	1 级 12 级 13 级 3R 级 4 级 4X 级
污染等级	3
额定工作电压	220 V DC Supply Circuit 220V DC V
连接容量	Flexible with Ferrule 1 x 0.75...2.5 mm ² Flexible with Ferrule 2 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 1 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 2 x 0.75...2.5 mm ² Flexible 1 x 0.75 ... 2.5 mm ² Flexible 2 x 0.75 ... 2.5 mm ² Solid 1 x 0.75...2.5 mm ² Solid 2 x 0.75...2.5 mm ²
连接类型	Screw Clamp
端子类型	Screw Terminals
拧紧力矩	0.9 N·m
剥线长度	8 mm

UL/CSA适用的技术参数

连接容量UL/CSA	1x 18...14 AWG 2x 18...14 AWG
------------	----------------------------------

环境条件

防护等级	Front IP66 Front IP67 Front IP69K Terminals IP20
------	---

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
---	-----------------

REACH Declaration	2CMT2022-006479
RoHS信息	2CMT2022-006498
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006523
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明 (文件编码)

CB认证	CQC_CN_CN50749
CQC认证	CQC2003010305054693
cULus 认证	UL_E496500-20171020
cURus 认证	UL_E496500-20171020
Declaration of Conformity - CCC	2020980305001187
符合性声明 - CE	2CMT2015-005451
Declaration of Conformity - UKCA	2CMT2020-006121
DNV GL Certificate	9AKK107046A3749
EAC认证	EAC-RU C-CN.ME77.B.00690_20

包装信息

1级包装单元	bag 10 piece
1级包装宽度	0.235 m
1级包装长度	0.125 m
1级包装高度	0.035 m
1级包装 总重	0.184 kg
1级包装 EAN	7320500475539

外部分类和标准

对象分类代码	P
ETIM 6	EC000272 - Indicator light complete
ETIM 7	EC000272 - Indicator light complete
ETIM 8	EC000272 - Indicator light complete
e级	V11.0 : 27371223
UNSPSC	39121534
IDEA 粒度分类代码 (IGCC)	4766 >> Indicator or pilot lights
E-Number (Finland)	2313545
E-Number (Norway)	4373530
E-Number (Sweden)	3705771

分类

低压产品及系统 → 控制产品 → 按钮指示装置 → Compact Range → CL Compact Pilot Lights

中压产品与系统 → 服务业务 → 备件 → Parts → All Spare Parts (Relays-SWG-CB)

