

### RSC-Series






The RSC-Series Super Curvette single pole rocker switches are physically similar to the Curvette Series. These switches offer higher electrical ratings with up to 125 amp peak inrush capability.

### Specifications

- Certifications\*: UL, CSA, VDE
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Polyester or Nylon

\* Due to ongoing technological advances, consult factory for certification specifics.

### Dimensional Specifications: in. [mm]



**MOUNTING HOLE**  
 Panel Thickness: .025 min. - .187 max.  
 Specific cutout dimension range dependent on panel thickness and material.  
 Consult factory.

<b>RSC</b>	<b>A</b>	<b>70</b>	<b>1</b>	<b>-</b>	<b>V</b>	<b>B</b>	<b>-</b>	<b>B</b>	<b>-</b>	<b>0</b>	<b>-</b>	<b>V</b>
<b>SERIES</b>	<b>RATING</b>		<b>TERMINATION</b>		<b>ACTUATOR STYLE</b>	<b>BASE COLOR<sup>1</sup></b>		<b>COLOR OF MOLDED-IN LEGEND AND/OR VISI-ROCKER END<sup>1</sup></b>				
RSC SINGLE POLE	60 15A 250VAC 20A 125VAC 3/4HP 125-250VAC 6(6)A 250VAC 50E3 T85		0 SOLDER LUG 1 .250TAB (QC)		R ROCKER V TWO COLOR VISI-ROCKER	B BLACK W WHITE		N NOT APPLICABLE B BLACK V VISI-RED W WHITE				
<b>CIRCUIT</b>			<b>ACTUATOR COLOR<sup>1</sup></b>		<b>ROCKER FACE LEGEND</b>							
A OFF-NONE-ON B ON-NONE-ON	61 15A 250 VAC 20A 125VAC 6(6)A 250VAC 50E3 T85		B BLACK W WHITE		MOLDED-IN <sup>2</sup>							
	70 15A 250VAC 20A 125VAC 3/4HP 125-250VAC 16(6)A 250VAC T85				INK TRANSFER							
	71 15A 250VAC 20A 125VAC 16(6)A 250VAC T85				STAMP <sup>3</sup>							
					0 NO LEGEND							
					1 OFF-ON (VERTICAL)							
					2 OFF-ON (HORIZONTAL)							
					8 O-I (HORIZONTAL)							
					9 O-I (VERTICAL)							
					ON-OFF (VERTICAL)							
					ON-OFF (HORIZONTAL)							
					OFF O-I ON (VERTICAL)							

**NOTES:**

Shading indicates standard configurations.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

1 Matte finish is standard. Custom colors are available. Consult factory.

2 Molded-in Legend available only with Visi-Rocker option.

3 White is standard with dark actuators; black is standard with light actuators.