

Features

- Adjustable height
- Dimensions of 840 x 1500 x 900mm
- Maximum load capacity of 300kg
- 20mm Thick Laminate Worktop

RS PRO Workbench, 300kg Max Load, Adjustable Height 650 → 900mm, 840 x 1500 x 900mm

RS Stock No.: 0324355



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Workbench, 300kg Max Load, 840 x 1500 x 900mm

You can adjust the height and configuration of this work bench from RS PRO to suit your needs. Its 20 mm laminated particleboard top provides you with a sturdy and damage-resistant surface that can hold a maximum weight of 300 kg. The frame is epoxy powder-coated for a scratch and corrosion-resistant finish.

The desk has a modular construction that allows you to adapt its shape to fit your space. You can also change the height of the work bench from 650 to 900 mm.

This work bench is designed to meet IEC (International Electrotechnical Commission) 61340-5-1 standards, meaning it won't damage your valuable electronic devices through electrostatic discharge (ESD). The desk is an excellent solution for use in light assembly, warehouse and packaging environments.

General Specifications

Type	Workbench only
Portable	No
Maximum Load	300kg
Length	840mm
Width	1500mm
Height	650 → 900mm, 1080 → 1550mm
Adjustable Height	Yes

Approvals

Declarations	REACH DoC
Standards Met	ISO 9001

Similar Products

Stock No.	Brand	Product Name	Dimension (mm)	Adjustable Height	Attribute
0440901	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1200 x 600	Yes	Kit: Rear Support Posts & Upper Shelf
0440902	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1200 x 900	Yes	Kit: Rear Support Posts & Upper Shelf
0440904	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1800 x 750	Yes	Kit: Rear Support Posts & Upper Shelf
0440905	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1800 x 900	Yes	Kit: Rear Support Posts & Upper Shelf
0440907	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1200 x 600	Yes	Workbench Only
0440908	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1200 x 900	Yes	Workbench Only
0440909	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1800 x 750	Yes	Workbench Only
0440910	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1800 x 900	Yes	Workbench Only
0324345	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1200 x 750	Yes	Kit: Rear Support Posts & Upper Shelf
0324346	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1500 x 600	Yes	Kit: Rear Support Posts & Upper Shelf
0324348	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1500 x 750	Yes	Kit: Rear Support Posts & Upper Shelf
0324349	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1500 x 900	Yes	Kit: Rear Support Posts & Upper Shelf
0324350	RS PRO	HEIGHT ADJUSTABLE WORKBENCH	840 x 1800 x 600	Yes	Kit: Rear Support Posts & Upper Shelf
0324351	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1200 x 750	Yes	Workbench Only
0324352	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1500 x 600	Yes	Workbench Only
0324354	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1500 x 750	Yes	Workbench Only

0324355	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1500 x 900	Yes	Workbench Only
0324357	RS PRO	WORKBENCH C/W HEIGHT LEG INSERTS	840 x 1800 x 600	Yes	Workbench Only