

5945VUM


Assortment of 199 tools for universal use in EVA foam trays

Universal use

19,6 kg

		art.
	059451011	5945VUM

- n. 21 **42:** combination wrenches
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- n. 9 **96BPC/SC9:** ball head offset hexagon key wrenches ○
1,5-2-2,5-3-4-5-6-8-10 mm
- n. 1 **895/1:** socket holder ○ 1/4 - □ 1/4
- n. 1 **895/3:** socket holder ○ 1/4 - □ 3/8
- n. 1 **895/6:** socket holder ○ 5/16 - □ 1/2
- n. 13 **900:** 1/4" hexagon sockets ○ 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 9 **900L:** hexagon hand sockets, long series ○ 5-6-7-8-9-10-11-12-13 mm
- n. 5 **900ME:** 1/4" socket drivers for hexagon screws ○ 3-4-5-6-7 mm
- n. 4 **900LP:** 1/4" socket drivers for slotted head screws ●
0,8x4-1x5,5x1,2x6,5-1,2x8 mm
- n. 4 **900PH:** 1/4" socket drivers for cross head Phillips® screws ⊕
PH1-PH2-PH3-PH4
- n. 7 **900TX:** socket drivers for Torx® head screws ⊙
T10-T15-T20-T25-T27-T30-T40
- n. 1 **900/16:** adaptor, 1/4" female and 3/8" male drives □ 1/4 - ■ 3/8
- n. 1 **900/20:** 1/4" drive extension bar 50 mm
- n. 1 **900/20L:** 1/4" drive extension bar 100 mm
- n. 1 **900/21:** 1/4" drive extension bar 150 mm
- n. 1 **900/25:** 1/4" drive universal joint
- n. 1 **900BG/30:** 1/4" drive spinner handle 176 mm
- n. 1 **900/42:** 1/4" drive swivel T-handle 115 mm
- n. 1 **900/55N:** 1/4" reversible ratchet ⊗ 125 mm
- n. 17 **910A:** 3/8" hexagon hand sockets ○
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22 mm
- n. 1 **910/15:** adaptor, 3/8" female and 1/4" male drivers □ 3/8 - ■ 1/4
- n. 1 **910/16:** adaptor, 1/2" female and 3/8" male drives □ 3/8 - ■ 1/2
- n. 1 **910/21:** 3/8" extension bar 125 mm
- n. 1 **910/22:** 3/8" extension bar 250
- n. 1 **910/25:** 3/8" drive universal joint
- n. 1 **910/42:** 3/8" drive sliding T - handle 210 mm
- n. 1 **910/55:** 3/8" reversible ratchet ⊗ 200 mm
- n. 21 **920A:** 1/2" square drive hexagon sockets ○
8-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-26-27-28-30-32 mm
- n. 1 **920/15:** adaptor, 1/2" female and 3/8" male drives □ 1/2 - ■ 3/8
- n. 1 **920/25:** 1/2" drive universal joint
- n. 1 **920AN:** 1/2" wobble extension bar 125 mm
- n. 1 **920AN:** 1/2" wobble extension bar 250 mm
- n. 1 **920/42:** 1/2" drive sliding T-handle 305 mm
- n. 1 **920/55:** 1/2" reversible ratchet ⊗ 275 mm
- n. 3 **956E:** 3/8" square drive spark plug sockets ○ 16 mm (5/8")-17,8



MM11



MM105



MM129



MM210



MM230

