

AF53 - Araflame Work Lightweight FR

Coverall

Collection: Araflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Araflame Work: 93% Meta Aramid, 5% Para Aramid, 2% Carbon Fibre, 150g

Outer Carton: 18

Product information

This super lightweight coverall offers outstanding flame resistant protection. The Araflame fabric is soft and breathable but provides excellent tear and tensile strength. Ideal for a variety of industries including oil and gas, petrochemical and many more. Coverall features include triple stitching throughout, secure pockets and waist elastication for ease of movement.

Araflame™ Work

Araflame™ Work has been developed for comfort and performance. Certified to several international standards, these garments offer outstanding protection at all times. The high quality fabric combined with the ergonomic fit provide all day comfort and style.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 3.8 CAL/CM², ATPV 4.5 CAL/CM²)

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV 5.9 CAL/CM² (HAF 63.1%))



Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- Sleeve pocket
- Two back patch pockets
- Triple-stitched seams for extra durability
- Durable, strong and long lasting brass zips
- Hook and loop cuffs for a secure fit
- Radio loop for easy clipping of a radio
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access
- CE-CAT III

AF53 - Araflame Work Lightweight FR Coverall

Commodity Code: 6211331000

Test House

Aitex (Notified Body No.: NB: 0161)
 Plaza Emilio Sala 1
 , ESPAGNE
 Cert No: 19/1623/01/0161

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
AF53NAR36	Navy	43.0	28.0	50.0	0.0800	0.0602	5036108257904	15036108747167
AF53NAR38	Navy	43.0	28.0	50.0	0.7480	0.0602	5036108257911	15036108747174
AF53NAR40	Navy	43.0	28.0	50.0	0.8040	0.0602	5036108257928	15036108747181
AF53NAR42	Navy	43.0	28.0	50.0	0.8140	0.0602	5036108257935	15036108747198
AF53NAR44	Navy	43.0	28.0	50.0	0.7920	0.0602	5036108257942	15036108747204
AF53NAR46	Navy	43.0	28.0	50.0	0.7980	0.0602	5036108257959	15036108747211
AF53NAR48	Navy	43.0	28.0	50.0	0.8500	0.0602	5036108257966	15036108747228
AF53NAR50	Navy	43.0	28.0	50.0	0.8320	0.0602	5036108257973	15036108747235
AF53NAR52	Navy	43.0	28.0	50.0	0.8640	0.0602	5036108257980	15036108747242
AF53NAR54	Navy	43.0	28.0	50.0	0.8620	0.0602	5036108257997	15036108747259