

Performance you can trust

SAFE STEP® Edge Sealer

Part Code: 43542
Pack Size: 100 ml tube with applicator nozzle

No of Pages	02
Issue No	05
Date	5/13
Ref	RES

Description

SAFE STEP® Edge Sealer is a synthetic bonding agent designed for use with the SAFE STEP® range of tapes and treads. It seals the edges and prevents the ingress of fluids, thereby increasing the durability of the tapes when exposed to wet conditions.

Features

- Quick and easy to apply.
- Increases life of SAFE STEP® Tapes and Treads.



Technical Data (Typical)

Colour:	Translucent white
Appearance:	Viscous tacky liquid
Chemical Type:	Solvent based nitrile polymer adhesive
Maximum Bond Strength Achieved:	After 2-7 days
Theoretical Coverage Per Pack:	10 m
Shelf Life:	12 months
Flash Point:	-18°C
Storage Conditions:	Store in a cool, dry, well ventilated place between 10-25°C. Away from direct sunlight and sources of ignition.
Flammability:	Highly Flammable
Heat Resistance:	-40 to +80°C
Application Temperature:	Above 5°C

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

Performance you can trust

Application

1. Ensure that the SAFE STEP® Tape or Tread is pressed firmly into position.
2. Use the applicator nozzle to apply a thin bead of SAFE STEP® Edge Sealer around the edge of the tape, tile or tread.
3. Allow 30 minutes minimum to cure, before walking over the surface.

For any specific advice regarding any aspect of this product, please consult our technical department.

Safe Step® Strong Bond and Edge Sealer Consumption Guide

Description	Product Code	Pack Size	500ml Strong Bond Tins Required (P/C 43541)	100ml Edge Sealer Tubes Required (P/C 43542)
SAFE STEP® Standard Tape				
25mm x 18.25m	43530	Single Roll	1	4
50mm x 18.25m	43531	Single Roll	1	4
100mm x 18.25m	43532	Single Roll	1	4
150mm x 18.25m	43533	Single Roll	1	4
SAFE STEP® Treads				
150mm x 600mm	43535	Pack of 10	1	2
	43534	Pack of 50	2	8
SAFE STEP® Hi-Vis Tape				
50mm x 18.25m	43540	Single Roll	1	4
SAFE STEP® Neutral Tape				
50mm x 18.25m	43539	Single Roll	1	4
SAFE STEP® Aqua Tape				
50mm x 18.25m	43538	Single Roll	Not to be used in conjunction with Strong Bond or Edge Sealer.	
SAFE STEP® Hazard Tape				
50mm x 18.25m	43547	Single Roll	1	4
SAFE STEP® Luminescent Tape				
50mm x 18.25m	43546	Single Roll	1	4

Coverage Rates (Typical)

Strong Bond	2.5m ² per 500ml tin
Edge Sealer	10m per 100ml tube

Limitations

Do not use with SAFE STEP® Aqua Tape.

Health & Safety

Refer to Safety Data Sheet before use. If further copies are required or for further information, please contact us at the address below:

Safety Data Sheets – Safety data sheets are available for download from our website www.rocol.com or may be obtained from your usual ROCOL® contact.

Disclaimer: The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which may affect the use and performance of our products, for this reason it is given without responsibility.

T +44 (0) 113 232 2600
 F +44 (0) 113 232 2740
 E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
 Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001
 Certificate No. FM 12448



BS EN ISO 14001
 Certificate No. EMS 67596



OHSAS 18001
 Certificate No. OHS 78173



INVESTOR IN PEOPLE