



 PRODUCT-DETAILS

2601/2 W-54

Switch Rocker/button, 2-pole switch alpine white - ocean



General Information

Extended Product Type	2601/2 W-54
Product ID	2CKA001085A1627
EAN	4011395083680
Catalog Description	Switch Rocker/button, 2-pole switch alpine white - ocean
Long Description	Switch, SM

Installation

Instructions and Manuals	No document needed
Wiring Diagram	2CKA000097E0043
Mounting Type	Surface Mounted
Type of Fastening	Mounting with Screw
Mounting Orientation	Vertical
Modular Components Included	Complete Device

Environmental

Degree of Protection	IP44
----------------------	------

Technical

Data Sheet, Technical Information	No document needed
Function	Function lighting: Label space
Number of Rocker Switches	1
Wiring Configuration	2-pole switch
Actuator Type	Rocker/button
Illumination	Optional
Terminal Type	Screwless Terminals

Electrical

Rated Voltage (U _r)	250 V
Rated Current (I _n)	10 A
Power Watt	LEDi / CFLi 100 W

Design

Design Range	ocean
Surface Finishing	Untreated Matt
Material	Thermoplastic
Label Space Provided	With Optional Label Space
Label Space Size	57.8 x 9.8 mm
RAL Number	Similar to RAL 9010
Color	alpine white

Dimensions

Product Net Width	74 mm
Product Net Height	83 mm
Product Net Depth / Length	55 mm
Product Net Weight	124 g

Engineering

Building Information Modeling – BIM	9AKK108466A8423
-------------------------------------	-----------------

Material Compliance

RoHS Declaration	2CKA200000E0315
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Declaration	2CKA309999E9999
REACH Information	True - contains substances > 0.1 mass percentage

REACH Date	20250901
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany
Simplified SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer

Certificates and Declarations

Declaration of Conformity - CE	2CKA200000E0315
EU Data Act Applicability and Compliance	Not Applicable

External Classifications and Standards

ETIM 9	EC001590 - Installation switch
ETIM 10	EC001590 - Installation switch
eClass	V11.0 : 27144053

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CKA001716A0042	Mounting Plate 1-gang brass	2609 WS	1	piece
2CKA001799A0882	Label Holder transparent - ocean	1763-53	1	piece
2CKA001784A0777	Illumination set Label holder LED 1 mA, 230 V clear transparent - ocean	2152 NLI-53	1	piece
2CKA001761A1510	Cable Entry alpine white - ocean	2086 W-54	1	piece
2CKA001761A1507	Cable Entry alpine white - ocean	2134 W-54	1	piece
2CKA001761A1508	Cable Entry alpine white - ocean	2136 W-54	1	piece
2CKA001761A1512	Cable Entry alpine white - ocean	2137/10 W-54	1	piece
2CKA001761A1513	Cable Entry alpine white - ocean	2137/11 W-54	1	piece
2CKA001761A1509	Cable bushing alpine white - ocean	2138 W-54	1	piece
2CKA001761A1511	Cable Entry alpine white - ocean	2139 W-54	1	piece

Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Surface Mounted Range → Mechanical Controls

