

## Features

- Heavy duty steel construction
- Adjustable spill retaining shelf
- Non removable sump
- Warning labels
- Conforms to COSHH guidelines
- Dimension 900 x 460 x 460mm

## RS PRO Yellow Lockable 1 Door Hazardous Substance Cabinet, 900 x 460 x 460mm

RS Stock No.: 0440915



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Hazardous Substance Cabinets

Our RS PRO hazardous substance cabinet is designed to provide safe storage for potentially dangerous substances and materials. Featuring steel construction, 2 Keys are provided with a chrome plated die-cast zinc handle (non snag) and a 2 point steel locking mechanism. A non-removable spillage sump is an integral part of the base to contain spillage. 1 adjustable shelf tray is provided which can retain minor spills and has a galvanised finish.

## General Specifications

|                   |        |
|-------------------|--------|
| Height            | 900mm  |
| Width             | 460mm  |
| Depth             | 460mm  |
| Lockable          | Yes    |
| Number of Doors   | 1      |
| Number of Shelves | 1      |
| Colour            | Yellow |

## Approvals

|               |           |
|---------------|-----------|
| Declarations  | REACH DoC |
| Standards Met | COSHH     |

## Similar Products

| Stock No. | Brand  | Product Name                                | Dimension       | No. of Door | Colour |
|-----------|--------|---------------------------------------------|-----------------|-------------|--------|
| 0440936   | RS PRO | Hazardous Cupboard<br>1800x1200x460mm       | 1800x1200x460mm | 2           | Yellow |
| 0440911   | RS PRO | Hazardous Cupboard<br>1800x900x460mm        | 1800x900x460mm  | 2           | Yellow |
| 0440913   | RS PRO | Hazardous Cupboard<br>1200x900x460mm        | 1200x900x460mm  | 2           | Yellow |
| 0440914   | RS PRO | Hazardous Cupboard<br>900x900x460mm         | 900x900x460mm   | 2           | Yellow |
| 0440915   | RS PRO | Hazardous Cupboard<br>900x460x460mm         | 900x460x460mm   | 1           | Yellow |
| 0440917   | RS PRO | Hazardous Cupboard<br>700x900x460mm         | 700x900x460mm   | 2           | Yellow |
| 0440918   | RS PRO | Hazardous Cupboard<br>700x350x300mm         | 700x350x300mm   | 1           | Yellow |
| 0440920   | RS PRO | Mobile Hazardous Cupboard<br>1040x900x460mm | 1040x900x460mm  | 2           | Yellow |
| 0440921   | RS PRO | Mobile Hazardous Cupboard<br>840x900x460mm  | 840x900x460mm   | 2           | Yellow |
| 0440923   | RS PRO | Flo.Chest Hazar. Cupboard<br>610x1170x460mm | 610x1170x460mm  | N/A         | Yellow |
| 0440924   | RS PRO | Wall Moun. Hazar. Cupboard<br>570x850x255mm | 570x850x255mm   | 2           | Yellow |
| 0440926   | RS PRO | Galvanised Extra Shelves<br>1200x460mm      | 1200x460mm      | N/A         | Yellow |
| 0440927   | RS PRO | Galvanised Extra Shelves<br>900x460mm       | 900x460mm       | N/A         | Yellow |
| 0440929   | RS PRO | Galvanised Extra Shelves<br>460x460mm       | 460x460mm       | N/A         | Yellow |
| 0440930   | RS PRO | Galvanised Extra Shelves<br>350x300mm       | 350x300mm       | N/A         | Yellow |
| 0440932   | RS PRO | Stand to suit 900x460mm                     | 900x460mm       | N/A         | Yellow |
| 0440933   | RS PRO | Stand to suit 460x460mm                     | 460x460mm       | N/A         | Yellow |
| 0440935   | RS PRO | Stand to suit 350x300mm                     | 350x300mm       | N/A         | Yellow |