



Socket

55

Product no. **05010027**
GTIN **4018754008742**
Model **55 27**



Label. 3/4 " Socket Size 27mm L.54mm

Properties.

- hex with AS-Drive profile
- 3/4" internal square drive
- HPQ® high performance steel, chrome-plated
- DIN 3124 / ISO 2725-1 / ASME B 107.5 M

Benefits.

Made in Germany - STAHLWILLE 3/4 " Socket 27 mm
Length 54 mm.

Product-specific forming - forged or cold-extruded -
ensures exceptional strength and durability.

hex AS-Drive, HPQ® high performance steel, chrome-
plated.

Extremely resilient, exceptionally durable.

Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical drawing.



Technical attributes.

Drive profile	hex AS-Drive
Square drive inner (inch)	3/4 "
d1	38,5 mm
d2	38 mm
d3	24 mm
DIN	DIN 3124 / ISO 2725-1, ASME B 107.5 M
Length mm (L)	54 mm
Size [mm]	27 mm
t1	20 mm
t2	26,8 mm

Logistics data.

Depth mm (IFS)	55
Width mm (IFS)	39
Height mm (IFS)	39
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	210
Width (packaged, mm)	62
Height (packaging, mm)	40
Volume (packaged, dm3)	0.5208 dm3
Product no.	05010027
Weight (gross, kg)	1,375
Weight PAP (kg)	0,000
Weight PVC (kg)	0,009
GTIN	4018754008742
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	5
Weight (g)	263 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
05010019	55 19	3/4 " Socket Size 19mm L.50mm	4018754008667
05010021	55 21	3/4 " Socket Size 21mm L.50mm	4018754008681
05010022	55 22	3/4 " Socket Size 22mm L.51mm	4018754008698

05010024	55 24	3/4 " Socket Size 24mm L.51mm	4018754008711
05010027	55 27	3/4 " Socket Size 27mm L.54mm	4018754008742
05010030	55 30	3/4 " Socket Size 30mm L.58mm	4018754008773
05010032	55 32	3/4 " Socket Size 32mm L.58mm	4018754008780
05010033	55 33	3/4 " Socket Size 33mm L.60mm	4018754008797
05010034	55 34	3/4 " Socket Size 34mm L.60mm	4018754008803
05010036	55 36	3/4 " Socket Size 36mm L.60mm	4018754008810
05010038	55 38	3/4 " Socket Size 38mm L.64mm	4018754008834
05010041	55 41	3/4 " Socket Size 41mm L.67mm	4018754008841
05010046	55 46	3/4 " Socket Size 46mm L.73mm	4018754008858
05010050	55 50	3/4 " Socket Size 50mm L.80mm	4018754008865
05010055	55 55	3/4 " Socket Size 55mm L.80mm	4018754008889
05010060	55 60	3/4 " Socket Size 60mm L.80mm	4018754008902

GTIN.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal