



partition 3WA, frame size 1, cable connection, 3 or 4-pole, compartment door W: 600 mm

| Model                                       |                  |
|---------------------------------------------|------------------|
| product brand name                          | SIVACON S4       |
| product designation                         | separation 3WL   |
| design of the product                       | cable connection |
| design of the surface                       | zinc plated      |
| General technical data                      |                  |
| design of pole                              | 4                |
| design                                      | assembly kit     |
| RAL color number                            | other            |
| color                                       | miscellaneous    |
| Product details                             |                  |
| product component                           |                  |
| • cable entry                               | No               |
| • lock                                      | No               |
| Mechanical Design                           |                  |
| height                                      | 550 mm           |
| width                                       | 600 mm           |
| depth                                       | 180 mm           |
| installation width for cabinet installation | 600 mm           |
| installation depth for cabinet installation | 180 mm           |
| shape of inner subdivisions                 |                  |
| • shape 2a                                  | No               |
| • shape 2b                                  | No               |
| • shape 3a                                  | Yes              |
| • shape 3b                                  | Yes              |
| • shape 4a                                  | No               |
| • shape 4b                                  | No               |
| net weight                                  | 5.1 kg           |
| material                                    | sheet-steel      |
| Certificates                                |                  |
| reference code according to IEC 81346-2     | UC               |
| Approvals Certificates                      |                  |
| General Product Approval                    | other            |

[Miscellaneous](#)



EG-Konf.



VDE



[Confirmation](#)

#### Further information

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-4BA01>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-4BA01>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ5000-4BA01](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-4BA01)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

---

last modified:

4/11/2025 

