




SFP28

TE Internal #: 2057500-1

SFP, SFP+ & zSFP+, Accessory, Data Rate (Max) 16 Gb/s, With Lightpipe, 1 x 1, Dual Round, Reduced Length, Standard, 1 Port

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP, SFP+ & zSFP+ > SFP accessories



Pluggable I/O Product Type: **Accessory**

Data Rate (Max): **16 Gb/s**

Lightpipe Options: **With Lightpipe**

Port Matrix Configuration: **1 x 1**

Lightpipe Configuration: **Dual Round**

[All SFP accessories \(17\)](#)

Features

Product Type Features

Form Factor	SFP+
Pluggable I/O Accessory Type	Lightpipe Kit
Cage Type	Single
Pluggable I/O Product Type	Accessory
Lightpipe Options	With Lightpipe

Configuration Features

Port Matrix Configuration	1 x 1
Lightpipe Configuration	Dual Round
Lightpipe Style	Reduced Length
Lightpipe Profile	Standard
Number of Ports	1

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Operation/Application

Heat Sink Compatible	No
For Use With Pluggable I/O Products	SFP+ Cage

Industry Standards



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-SF59-C117ST123
SFP+ Stacked Cage Assemblies



TE Part # CAT-C11-H50626
SFP+ to SFP+ I/O Cable Assembly: 30 AWG



TE Part # 2007194-2
SFP+ 1x1 Cage Assembly, PCI, Solder Tail




TE Part # 2007194-1
SFP+ 1x1 Cage Assembly, PCI, Solder Tail



TE Part # 2110304-1
SFP+ 1x1 Cage Assembly, Solder Tail



TE Part # 2007464-3
SFP+ 1x1 Cage Assy, PF,with Heatsink



TE Part # 2007198-1
SFP+ 1x1 Cage Assembly, Press-



TE Part # 2007464-2
SFP+ 1x1 Cage Assy, PF,with Heatsink



TE Part # 2007198-2
SFP+ 1x1 Cage Assembly, Press-Fit



TE Part # 2007464-1
SFP+ 1x1 Cage Assy, PF,with Heatsink



TE Part # 2007215-1
SFP+ 1x1 Cage Assy, PCI, Press



TE Part # 2007193-1
SFP+ 1x1 Cage Assembly, PCI, S



TE Part # 2007277-1
SFP+ 1x1 Cage Assy, PCI, PF, Heatsink



TE Part # 2057159-1
SFP+ 1x1 Cage Assy, Press-Fit, 20 Pin



TE Part # 2170193-1
SFP+ 1x1 Cage Assembly,w/ Light Pipe



TE Part # CAT-SF59-AC229
SFP accessories



TE Part # 2057086-2
SFP+ Enhanced 1x1 Cage Assembly



TE Part # 2057021-1
SFP+ 1x1 Cage Assy, Short Solder Tail



TE Part # 2007215-2
SFP+ 1x1 Cage Assy, PCI, Press Fit



TE Part # 2057085-4
SFP+ 1x1 Enhanced, Gasket, Pre

Documents

Product Drawings
Light Pipe, Ganged SFP+
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2057500-1_A.2d_dxf.zip
English



Customer View Model

[ENG_CVM_CVM_2057500-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2057500-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English